

Kemtron | Kemtron 1202 Series

TE Internal #: 2418197-1


Extruded EMI Gasket, Conductive Strip, Silicone Binding, Silver

Plated Aluminum (Ag/Al) Filler, Tube, Length 10 m [32.8 ft],

Kemtron 1202 Series

[View on TE.com >](#)

EMI & EMC Solutions > EMI Shielding > EMI Gaskets > Extruded EMI Gasket Conductive Strip



Gasket Type: Extruded EMI Gasket

Finished Type: Conductive Strip

Binding Material: Silicone

Filler Material: Silver Plated Aluminum (Ag/Al)

Gasket Shape: Tube

[All Extruded EMI Gasket Conductive Strip \(56\)](#)

Features

Body Features

Gasket Type	Extruded EMI Gasket
Gasket Shape	Tube

Product Type Features

Finished Type	Conductive Strip
Binding Material	Silicone
Filler Material	Silver Plated Aluminum (Ag/Al)

Dimensions

Product Length	10 m[32.8 ft]
Outside Diameter	2.6 mm[.102 in]
Inside Diameter	1.1 mm[.043 in]

Usage Conditions

Operating Temperature Range	-55 – 160 °C[-67 – 320 °F]
-----------------------------	----------------------------

Electrical Characteristics

Resistance to Petroleum	No
Volume Resistivity (Max)	.008 Ω.cm

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: DCP (.22% in Component)
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2452645-1
SNA Tube 2.6mm OD x 1.1mm ID x
10m L



TE Part # CAT-EMIG-0001
Extruded EMI Gasket Conductive Strip

Also in the Series | Kemtron 1202 Series



EMI Gaskets(36)



Medical EMI & EMC Solutions(36)

Customers Also Bought



TE Part #5749111-6
68 50SR CABLE PLUG ASSY



TE Part #5788796-1
09 HTMSFL ASSY RA 318 (IN,BL)



TE Part #1-5750913-7
68 50SR CABLE CONN KIT



TE Part #2420742-1
SSA Tube 2.6mm OD x 1.1mm ID x 1m
L



TE Part #5-747904-5
9 Plug Solder Cup, 30 gold, Ro



TE Part #667353-000
CWT-1501



TE Part #464766-E
SRCROL A 2,54 2 C2426 500 137 *
9999 J 2



TE Part #952050-E
VORCSI SRC CRIMP ZANGE- ROLLE
284070 J 3



TE Part #992216-E
VORCSI SRC CRIMP ZANGE- ROLLE
374039 J 3



TE Part #1734592-8
FPC CONN. 0.5MM PITCH B/C, 8P

Documents

Product Drawings

[SSA Tube 2.6mm OD x 1.1mm ID x 10m L](#)

English

Datasheets & Catalog Pages

[Performance Materials brochure](#)

English

Datasheet - Conductive Elastomers

English

Product Specifications

[Application Specification](#)

English