

# HC-HPR-B16-BFH-EMR-BK - Housing



1411060

<https://www.phoenixcontact.com/us/products/1411060>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON B16 panel mounting base, HPR series, for screw locking, for increased environmental and EMC requirements

## Your advantages

- Vibration and shock: IEC 61373/EN 50155, category 1, class 1B

## Commercial data

Item number	1411060
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF60
Product key	BF7AAI
Catalog page	Page 628 (C-4-2015)
GTIN	4046356921619
Weight per piece (including packing)	180.61 g
Weight per piece (excluding packing)	167.23 g
Customs tariff number	85389099
Country of origin	CN

# HC-HPR-B16-BFH-EMR-BK - Housing



1411060

<https://www.phoenixcontact.com/us/products/1411060>

## Technical data

### Notes

General	For contact inserts HC-B16, BB32, BBB40, D40, DD72, HS6, M, K
---------	---


### Product properties

Product type	Housing with screw locking
Housing type	Panel mounting base
Product family	HC-HPR-B
Series	HPR-B16
Application	Railway applications
Type	B16
Protective cover	no
Pg screw connection	none

### Connection data

Tightening torque	4 Nm (Locking screw)
-------------------	----------------------

### Dimensions

Dimensional drawing	
Width	58 mm
Height	20 mm
Length	165 mm
Drill hole distance, horizontal	103 mm
Drill hole distance, vertical	32 mm
Hole diameter	6.5 mm

### Installation dimensions

Width of the assembly cutout	35 mm
Length of the assembly cutout	82 mm

### Material specifications

Seal material	NBR
Housing material	Die-cast aluminum
Housing surface material	Powder-coated, black
Locking latch material	Stainless steel
Material of locking screw	Stainless steel

### Environmental and real-life conditions

# HC-HPR-B16-BFH-EMR-BK - Housing



1411060

<https://www.phoenixcontact.com/us/products/1411060>

## Ambient conditions

Degree of protection	IP66
	IP68 (0.5 bar / 24 h)
	IP69 (ISO 20653:2013-02)
Impact strength	IK09
Ambient temperature (operation)	-40 °C ... 125 °C

## Mechanical properties

### Mechanical data

Locking type	Nut
--------------	-----

# HC-HPR-B16-BFH-EMR-BK - Housing


1411060

<https://www.phoenixcontact.com/us/products/1411060>




## Drawings

Dimensional drawing



Dimensional drawing



Mounting cutout

# HC-HPR-B16-BFH-EMR-BK - Housing



1411060

<https://www.phoenixcontact.com/us/products/1411060>

## Approvals

💡 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1411060>

### DNV

Approval ID: TAE000037S



### EAC

Approval ID: RU C-DE.AI30.B.01102

# HC-HPR-B16-BFH-EMR-BK - Housing



1411060

<https://www.phoenixcontact.com/us/products/1411060>

## Classifications

### ECLASS

ECLASS-11.0	27440202
ECLASS-12.0	27440202
ECLASS-13.0	27440202

### ETIM

ETIM 9.0	EC000437
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# HC-HPR-B16-BFH-EMR-BK - Housing



1411060  
<https://www.phoenixcontact.com/us/products/1411060>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)