




Wire Protection & Management > Interconnect Devices > Shielded Contacts



Compatible With Wire & Cable Type: **TriAxial**

Contact Type: **Socket**

Contact Size: **Size 8**

EU RoHS Compliance: **Not Compliant**

EU ELV Compliance: **Not Compliant**

Features

Usage Conditions

Operating Temperature (Max)	150 °C
-----------------------------	--------

Configuration Features

Compatible With Wire & Cable Type	TriAxial
-----------------------------------	----------

Contact Features

Contact Type	Socket
Contact Size	Size 8

Other

EU RoHS Compliance	Not Compliant
EU ELV Compliance	Not Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (37% in Solder) <small>Article Safe Usage Statements:</small>



Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 750984-004
[10612-24-9](#)


Customers Also Bought




TE Part #CAT-R21-56701
Convoluted Heat Shrink Uni Boots:
Lipped, Straight




TE Part #865421-000
[D-602-0150](#)




TE Part #2332587-1
[NETT WARRIOR FRONT PANEL MT, RECEPT, PCB](#)




TE Part #ZPF000000000012692
[DBAS 70-61-0 PN 090 A5673](#)




TE Part #ZPF000000000012699
[DBAS 70-61-0 PN-A5619](#)



TE Part #ZPF000000000013952
[DBAS 78G 61-0 SN 090 A5673](#)



TE Part #YDTS26W11-98BN0000
[PLUG ASSY](#)



TE Part #ZPF000000000007131
[9-741-8003-00](#)



Documents

Product Drawings

DK-602-0157-2

English

Datasheets & Catalog Pages

Data Bus Components Brochure

English

Product Specifications

Installation Procedure for DK-602-0156 and -0157 Triaxial Contacts

English

Installation Procedure for DK-602-0156 and ?0157 Triaxial Contacts