



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **2**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-2**

Features

Dimensions

Product Length	24.38 mm[.96 in]
----------------	------------------

Packaging Features

Packaging Quantity	1
Packaging Method	Carton

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Product Type Features

Connector & Contact Terminates To	Wire & Cable
Sealable	No
Connector System	Wire-to-Board, Wire-to-Wire
Connector & Housing Type	Receptacle



Configuration Features

Number of Positions	2
---------------------	---

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	With

Housing Features

Housing Material	Nylon
Centerline (Pitch)	15.11 mm[.595 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1217092-1 PL 250 TERMINAL RECEPTACLE 16-12 AWG BR	 TE Part # 63854-1 250 PL MKIII REC. 18-14AWG BR	 TE Part # 63933-2 250 PL MKIII REC. 22-18AWG TPBR	 TE Part # 63854-2 250 PL MKIII REC. 18-14AWG TPBR
 TE Part # 1-521119-1 POSILOCK HSG.,250 SRS,MKIII,2P,V0, NAT	 TE Part # 63933-1 PL .250 TERMINAL REC 22-18 AWG BR	 TE Part # 1217092-2 PL 250 TERMINAL REC 16-12 AWG TPBR	

Also in the Series | Mark III

 Crimp Terminal Housings(184)	 Quick Disconnects(185)
---	--

Also in the Series | Positive Lock 250



Automotive Terminals(1)



Crimp Terminal Housings(184)



Insertion & Extraction Tools(3)



Insulation Boots & Sleeves(4)




Quick Disconnects(185)


Customers Also Bought



TE Part #104257-7
08 MTE RCPT HSG SR LATCH .100



TE Part #2-520856-2
ULTRA-FAST 250 ASY REC 22-18 TPBR



TE Part #2-520181-2
ULTRA-FAST 187 ASY REC 22-18 AWG TPBR




TE Part #1-104257-1
12 MTE RCPT HSG SR LATCH .100




TE Part #1062-16-0722
SOC, SF, SIZE 16, 14-18, NI/SN



TE Part #EM6977-000
X4-0.6-0-SP




TE Part #5-103944-1
8X2 MTE SHRD PIN SR POL .100CL



TE Part #3-520150-2
ULTRA-FAST 187 ASY REC 16-14 AWG TPBR



TE Part #62384-1
110 FASTON TAB 22-18 AWG TPBR



TE Part #1601637-1
L076/0926R16BX=MTM 1800-4600

Documents



Product Drawings

PL 250 HOUSING RECEPTACLE NYLON 6/6

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_521119-1_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_521119-1_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_521119-1_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FASTON Housings

English

Positive Lock Receptacles

English

1654742_HOUSEHOLD_APPLIANCES_RAST5

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English