




Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Base Housing**

Hood & Base Locking Device Type: **Screwlock**

Sealable: **Yes**

EU RoHS Compliance: **Compliant**

EU ELV Compliance: **Compliant**

Features

Usage Conditions

Corrosion Protected	Yes
---------------------	-----

Housing Features

Housing Material	Die Cast Aluminum
------------------	-------------------

Mechanical Attachment

Locking Device Location	Hood
Hood & Base Locking Device Type	Screwlock

Product Type Features

Hood & Base Connector Product Type	Base Housing
Sealable	Yes

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T1922062125-000  
H6BPR-TGHC-M25



TE Part # T1922062121-000  
H6BPR-TGHC-PG21



TE Part # T1922062116-000  
H6BPR-TGHC-PG16



TE Part # T1922062129-000  
H6BPR-TGHC-PG29



TE Part # T1912062116-000  
H6BPR-TSHC-PG16



TE Part # T1922062132-000  
H6BPR-TGHC-M32



TE Part # T1912062125-001  
H6BPR-TSHC-M25



TE Part # T1922061140-000  
H6BPR-TGHC-M40



TE Part # T1912062125-000  
[H6BPR-TSHC-M25](#)

TE Part # T1912062121-000  
[H6BPR-TSHC-PG21](#)

Customers Also Bought

TE Part #W8P  
WEDGE LOCK, 8P, REC, GRN, DT

TE Part #1060-16-0622  
PIN, SF, SIZE 16, 16-20, NI/SN

TE Part #5-160558-2  
FF 250 REC 0.5-1.5MM2 TPBR

TE Part #160002  
TERM,SOLIS R 2 M10

TE Part #0460-264-16141  
PIN, SOLID, SIZE 16, 16-20AWG, NI

Documents

Product Drawings

[H6BPR-AGC](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_T1932062000-000\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_T1932062000-000\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_T1932062000-000\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

HEAVY DUTY CONNECTORS

English

HEAVY DUTY CONNECTORS

Japanese

Product Specifications

Application Specification

English

Application Specification