




Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Shield Assembly**

Cable Exit Angle: **180°**

Strain Relief: **Without**

Primary Product Color: **Black**

Primary Product Material: **PBT GF**

Features

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Dimensions

Compatible Cable Bundle Diameter Range	4.3 mm[.169 in]
--	-----------------

Packaging Features

Packaging Method	Carton
------------------	--------

Other

Serviceable	Yes
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Type Features

Protection & Strain Relief Accessory Type	Shield Assembly
---	-----------------

Body Features

Cable Exit Angle	180°
Primary Product Color	Black
Primary Product Material	PBT GF

Mechanical Attachment

Strain Relief	Without
---------------	---------

Configuration Features



Number of Positions	18
---------------------	----

Usage Conditions

Operating Temperature (Max)	80 °C, 105 °C, 90 °C, 100 °C, 85 °C, 75 °C, 70 °C, 110 °C, 120 °C[212 °F]
Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1355349-1
MQS ABDECKKAPPE 18P

TE Part # 1355348-1
18POS MQS REC

TE Part # 1-1355154-1
MQS STIFTWANNE 18P

Customers Also Bought

TE Part #CAT-M8793-CH8172
MQS, CONNECTOR HOUSING

TE Part #4-1718353-2
2 POS TAB HSG 5.8x0.8MM

TE Part #2302454-9
1-PORT MATENET FRAME,UTP, COD Z

TE Part #2302456-9
6-PORT MATENET FRAME, UTP, COD Z

TE Part #2-1355350-1
MQS COVER 18POS

TE Part #1813395-1
ER70 GM DELTA II

TE Part #2362767-3
MATENET,CABLE ASSY,1 GBPS UTP

TE Part #K1161960-1
Plunger Switch 44-01-074 C4314

TE Part #K1161961-1
Plunger Switch 44-01-076 C4314

Documents

Product Drawings
MQS ABDECKKAPPE 18P
English

CAD Files
3D PDF
English

Customer View Model
ENG_CVM_1-1355350-1_A1.2d_dxf.zip



English

Customer View Model

[ENG_CVM_1-1355350-1_A1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1-1355350-1_A1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Micro Quardlok System Female Connectors

English

Product Specification

English