

MMZ1608A152ETA00



Applications



Commercial Grade

Feature

High Speed

High speed signal line

GHz

High Wide Z

High Z for Wide Band

Series


MMZ

Status



Production (Not Recommended for New Design)

Recommended Alternate Part No. : [MMZ1005A152ET000](#)



Size

Length(L)	1.60mm ±0.15mm
Width(W)	0.80mm ±0.15mm
Thickness(T)	0.80mm ±0.15mm
Recommended Land Pattern (A)	0.60mm Nom.
Recommended Land Pattern (B)	0.80mm Nom.
Recommended Land Pattern (C)	0.80mm Nom.

Electrical Characteristics

Impedance at 100MHz	1kΩ Min.
Rated Current	300mA
DC Resistance (Max.)	1Ω

Other

Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125°C
Soldering Method	Reflow Iron Soldering
AEC-Q200	No
Packing	Punched (Paper)Taping [180mm Reel, Tape width 8mm]
Package Quantity	4000pcs
Weight	0.004g



! Images are for reference only and show exemplary products.

! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.



Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)





Associated Images

