



Switches > Battery Disconnect Switches > Battery Disconnect, 200A, 1 Pole



Switch Main Contact Current Rating: 250 A

Operating Voltage: 32 VDC

Number of Poles: 1

Operating Handle Type: Double Wing Handle

Termination Thread Size: M8

[All Battery Disconnect, 200A, 1 Pole \(30\)](#)

Features

Product Type Features

Sealed Device	Yes
---------------	-----

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Dimensions

Screw Hole Diameter	7 mm[.276 in]
Centerline Between Flange Screw Holes	38 mm[1.5 in]

Electrical Characteristics

Operating Voltage	32 VDC
Switch Main Contact Current Rating	250 A

Configuration Features

Number of Poles	1
Number of Auxiliary Contacts	0
Switch Keying Option	Not Removable

Mechanical Attachment

Operating Handle Type	Double Wing Handle
-----------------------	--------------------



Termination Thread Size	M8
Switch Mounting Option	Round Flange

Body Features

Operating Handle Color	Black
------------------------	-------

Other

EU RoHS Compliance	Not Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (2% in Component part) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | **KISSLING Series 35**



Customers Also Bought





Documents

Product Drawings

Battery Disconnecter 35-210-041-S

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_35-210-041-S\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_35-210-041-S\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_35-210-041-S\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

KISSLING SINGLE POLE BI-STABLE RELAYS Series 30 / 300A

English

KISSLING BATTERY DISCONNECTOR Series 35 / 200A

English