

PSH 3- 6 500MM - Shield connection clamp



3061525

<https://www.phoenixcontact.com/us/products/3061525>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shield connection clamp, nom. voltage: 300 V, color: black

Your advantages

- Connected shielded cable is fixed using a cable binder
- Snapped into strain relief once the plug has been wired
- The connecting cable for the shielding is connected via the plug and then makes direct contact with the terminal block when inserted
- For connecting shielded cables

Commercial data

Item number	3061525
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE02
Product key	BE214Z
Catalog page	Page 364 (C-1-2019)
GTIN	4046356592895
Weight per piece (including packing)	10.1 g
Weight per piece (excluding packing)	9.58 g
Customs tariff number	85444290
Country of origin	PL

PSH 3- 6 500MM - Shield connection clamp



3061525

<https://www.phoenixcontact.com/us/products/3061525>

Technical data

Product properties

Product type	Shield connection
--------------	-------------------

Material specifications

Color	black (RAL 9005)
Material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

PSH 3- 6 500MM - Shield connection clamp



3061525

<https://www.phoenixcontact.com/us/products/3061525>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3061525>



EAC

Approval ID: EACKZ 08593

PSH 3- 6 500MM - Shield connection clamp



3061525

<https://www.phoenixcontact.com/us/products/3061525>

Classifications

ECLASS

ECLASS-11.0	27141190
ECLASS-12.0	27141190
ECLASS-13.0	27250192

ETIM

ETIM 9.0	EC002848
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PSH 3- 6 500MM - Shield connection clamp



3061525

<https://www.phoenixcontact.com/us/products/3061525>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com