




Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Strain Relief Cover**

Number of Positions: **64**

Operating Temperature (Max): **105 °C [ 221 °F ]**

Operating Temperature Range: **-55 – 105 °C [ -67 – 221 °F ]**

EU RoHS Compliance: **Compliant**

Features

Housing Features

Compatible With Connector Shape	D-Shaped
---------------------------------	----------

Mechanical Attachment

Strain Relief	With
---------------	------

Packaging Features

Packaging Method	Box, Package, Kit
Packaging Quantity	100

Product Type Features

Connector Cover Type	Strain Relief Cover
----------------------	---------------------

Configuration Features

Number of Positions	64
---------------------	----

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | CHAMP Docking Connectors



Connector Caps & Covers(31)



Connector Hardware(28)



Connector Strain Relief(2)



Docking Connectors(19)



IDC D-Sub Connectors(55)


Customers Also Bought



TE Part #5229912-1  
KIT, PLUG, 50 POS,B SLOT C/LOK



TE Part #CAT-035-DCCPB20  
D-Sub Connector Contacts: Pin, Brass, Signal, Size 20




TE Part #552082-1  
180 DEG COVER KIT 64 POS



TE Part #208262-3  
5009-328-0022



TE Part #5228980-7  
JACK,BHD,COML,SERIES BNC,GOLD



TE Part #5745583-1  
UNIV SLIDLTCH KIT SZ 2



TE Part #1-456402-5  
CRIMPER WIRE .055 F



TE Part #6-23629-0  
PIN,STRAIGHT,GROOVED



TE Part #4903756016  
RT-375-1/2-X-65MM

Document



Product Drawings

COVR,KIT,180DEG,64POS,0.610 CA

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_569025-1\_C.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_569025-1\_C.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_569025-1\_C.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English