

2267088-5

✓ ACTIVE


Alcoswitch

TE Internal #: 2267088-5

.4 A Toggle Switch, Single Pole - Double Throw Configuration (Pole-Throw), On On, 2 Position, 20 VDC, 20 VAC, Board Mount, Process Sealed

[View on TE.com >](#)

Switches > Toggle Switches

Contact Current Rating: **.4 A**Configuration (Pole-Throw): **Single Pole - Double Throw**Operating Function: **On On**Number of Positions: **2**Operating Voltage: **20 VDC**

Features

Product Type Features

Sealed Device	Yes
Switch Connection Type	Printed Circuit
Switch Type	Rocker Switch

Electrical Characteristics

Contact Current Rating	.4 A
Operating Voltage	20 VAC

Configuration Features

Configuration (Pole-Throw)	Single Pole - Double Throw
Operating Function	On On
Number of Positions	2

Mechanical Attachment

Product Mount Type	Board Mount
--------------------	-------------

Housing Features

Process Sealed

Yes

Contact Features

Switch Contact Plating Material

Gold

Termination Features

Termination Method to PCB

Through Hole - Solder

Other

EU RoHS Compliance

Compliant with Exemptions

EU ELV Compliance

Compliant

Product ComplianceFor compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2024 (241)

Candidate List Declared Against: JUNE 2024 (241)

SVHC > Threshold:

Pb (4% in Component Part)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free

Solder Process Capability

Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



Documents

Product Drawings

[RAS1R102M7RES](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2267088-5_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2267088-5_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2267088-5_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Subminiature Switches

English