



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Base Housing**

Cable Entry Location: **Bottom**

Hood & Base Locking Device Type: **Screwlock**

Sealable: **Yes**

EU RoHS Compliance: **Compliant**

Features

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Type Features

Hood & Base Connector Product Type	Base Housing
Sealable	Yes

Body Features

Cable Entry Location	Bottom
----------------------	--------

Mechanical Attachment

Hood & Base Locking Device Type	Screwlock
---------------------------------	-----------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # T1912101132-000 H10BPR-TSHC-M32	 TE Part # T1912101121-000 H10BPR-TSHC-PG21	 TE Part # T1922101121-000 H10BPR-TGHC-PG21	 TE Part # T1912101120-000 H10BPR-TSHC-M20
 TE Part # T1912101116-000 H10BPR-TSHC-PG16	 TE Part # T1902101232-000 H10BPR-TS/GHC-2M32	 TE Part # T1922101125-000 H10BPR-TGHC-M25	 TE Part # T1902101229-000 H10BPR-TS/GHC-2PG29



			
TE Part # T1912101125-000 H10BPR-TSHC-M25	TE Part # T1902101240-000 H10BPR-TS/GHC-2M40	TE Part # T1922101120-000 H10BPR-TGHC-M20	TE Part # T1902101225-000 H10BPR-TS/GHC-2M25
			
TE Part # T1922101116-000 H10BPR-TGHC-PG16	TE Part # T1912101129-000 H10BPR-TSHC-PG29	TE Part # T1922101129-000 H10BPR-TGHC-PG29	TE Part # T1922101132-000 H10BPR-TGHC-M32

Customers Also Bought

			
TE Part #T2020082201-000 HD-008-F	TE Part #1-480711-9 15P UMNL CAP HSG BLK	TE Part #T2106062201-000 HWK6/6-012-F	TE Part #640250-1 01P SL156 HSG W/LCK RAMP NATL
			
TE Part #T0931003003-000 CODING-PIN-M3	TE Part #1SNA195638R2300 M4/6.4A.P	TE Part #T1730060000-000 H6B-TBF-T	TE Part #T2120100219-000 ZGG-10DSTK,1-7,2-8,3-9,4-6,5-10
			
TE Part #T2120100220-000 ZGGP-H10BSK 1-7/2-8/3-9/4-6/5-10	TE Part #1473203-1 025 CAP ASSY 16P P/BACK BRCKT		

Documents



Product Drawings

H10BPR-AGC

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T1932101000-000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T1932101000-000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T1932101000-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

HEAVY DUTY CONNECTORS

Japanese

Product Specifications

Application Specification

English

Application Specification