


RBO 5-F/8 - Bolt connection terminal block



3058253

<https://www.phoenixcontact.com/us/products/3058253>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block with bolt connection method, cross section: 0.1 - 6 mm², AWG: 26 - 10, width 13 mm, color: gray

Your advantages

- Direct mounting in control boxes
- Compact connection with ring and fork-type cable lugs
- Bridge shaft for potential distribution using standard screw bridges
- Isolator bridge bar for switchable cross connections

Commercial data

Item number	3058253
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE44
Product key	BE4415
Catalog page	Page 387 (C-1-2019)
GTIN	4046356534789
Weight per piece (including packing)	184.3 g
Weight per piece (excluding packing)	184.3 g
Customs tariff number	85369010
Country of origin	IN

RBO 5-F/8 - Bolt connection terminal block



3058253

<https://www.phoenixcontact.com/us/products/3058253>

Technical data

Product properties

Product type	Bolt connection terminal block
Pitch	13 mm
Number of connections	16
Number of rows	1
Potentials	8

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	1.82 W

Connection data

Number of connections per level	16
Nominal cross section	10 mm ²

1 level

Stripping length	The stripping length depends on the specification provided by the cable lug manufacturer.
Connection in acc. with standard	IEC 60947-7-1
Nominal current	57 A
Maximum load current	57 A (with 10 mm ² conductor cross section)
Nominal voltage	800 V
Nominal cross section	10 mm ²

Cable lug connection DIN 46234:1980-03

Connection in acc. with standard	DIN 46234:1980-03
Cross section	0.1 mm ² ... 10 mm ²
Cross section range AWG	26 ... 8 (converted acc. to IEC)
Hole diameter	5.3 mm
Width	10 mm
Bolt diameter	5 mm
Screw thread	M5
Tightening torque	2 ... 2.2 Nm
Connection in acc. with standard	DIN 46237:1970-07
Cross section	0.5 mm ² ... 6 mm ²
Cross section range AWG	20 ... 10 (converted acc. to IEC)
Hole diameter	5.3 mm
Width	10 mm
Bolt diameter	5 mm

RBO 5-F/8 - Bolt connection terminal block



3058253

<https://www.phoenixcontact.com/us/products/3058253>

Tightening torque	2 ... 2.2 Nm
Identification color of ring cable lugs : red	1 mm ²
Identification color of ring cable lugs : blue	2.5 mm ²
Identification color of ring cable lugs : yellow	6 mm ²

Dimensions

Width	121.7 mm
Height	53.3 mm
Depth	37 mm
Hole diameter	5.2 mm
Pitch	13 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

RBO 5-F/8 - Bolt connection terminal block



3058253

<https://www.phoenixcontact.com/us/products/3058253>

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

Mounting

Mounting type	direct screw connection
---------------	-------------------------

RBO 5-F/8 - Bolt connection terminal block

3058253

<https://www.phoenixcontact.com/us/products/3058253>



Drawings

Circuit diagram



RBO 5-F/8 - Bolt connection terminal block



3058253

<https://www.phoenixcontact.com/us/products/3058253>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3058253>

 UL Recognized Approval ID: FILE E 60425				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
Use group B	600 V	45 A	-	-
Use group C	600 V	45 A	-	-

 EAC Approval ID: RU C-DE.BL08.B.00540				
---	--	--	--	--

 EAC Approval ID: EACKZ 08593				
--	--	--	--	--

RBO 5-F/8 - Bolt connection terminal block



3058253

<https://www.phoenixcontact.com/us/products/3058253>

Classifications

ECLASS

ECLASS-11.0	27141120
ECLASS-13.0	27250101

ETIM

ETIM 9.0	EC000897
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RBO 5-F/8 - Bolt connection terminal block



3058253

<https://www.phoenixcontact.com/us/products/3058253>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com