

Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant with Exemptions |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Cadmium oxide (7.95% in Component part) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content | Not Low Halogen - contains Br or Cl > 900 ppm. |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | [Potter & Brumfield W9](#)



Circuit Breakers(62)

Customers Also Bought



TE Part #2-1419106-1
27E489=SOCKET,K10,8,PCB,NYL



TE Part #1-480304-0
03P CMNL PLUG HSG P/M NATL



TE Part #60617-4
CMNL SOK PTPPHBZ L/P




TE Part #5-1393144-0
K10P-11DT5-12=K10/K20




TE Part #3-1393254-4
W91-X113-10=M6/M7/M9/W6/W7



TE Part #3-1393254-5
W91-X113-15=M6/M7/M9/W6/W7



TE Part #2-966067-3
FER,WIRE,PL SLV,6.00/10,L18,YELLOW, LP



TE Part #236891-000
22759/44-22-0

Documents

- CAD Files

Customer View Model

ENG_CVM_CVM_2-1393255-3_D.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1393255-3_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1393255-3_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

- Datasheets & Catalog Pages

W6/W9 Magnetic Hydraulic Circuit Breaker

English



Agency Approvals

UL

English