




Connectors > D-Shaped Connectors > Microminiature & Nanominiature D Connectors



Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Board**
Number of Positions: **9**
Centerline (Pitch): **1.27 mm [.05 in]**
Sealable: **No**

Features

Contact Features

Contact Type	Socket
Contact Options	Installed

Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Method to Wire & Cable	Preterminated Flying Leads

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	9
---------------------	---

Housing Features

Centerline (Pitch)	1.27 mm[.05 in]
--------------------	-----------------

Operation/Application

Circuit Application	Power
---------------------	-------

Other

--



EU RoHS Compliance	Not Compliant
EU ELV Compliance	Not Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (.4% in Plating in pins) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought

STM009M5CN

Receptacle, Wire-to-Board, 9 Position, 1.27 mm [.05 in] Centerline, Printed Circuit Board, Power, Microminiature & Nanominiature D Connectors



TE Part #2102735-1
BP, Half Left End, MULTIGIG RT 2R

TE Part #2102736-1
BP, Center, MULTIGIG RT 2R

TE Part #2102771-1
DC, 7Row, Center, MULTIGIG RT 2R

TE Part #1676221-2
RN 0805 1K0 0.1% 10PPM 1KRL

TE Part #MS561101BA03-50
MS5611 BAROMETRIC SENSOR CM T&R

TE Part #4-1879133-4
RN 0603 2K49 0.1% 10PPM 1K RL

TE Part #1676303-2
RN 0805 31K6 0.1% 10PPM 1KRL

TE Part #1676385-3
RN 0805 5K11 0.1% 10PPM 5KRL

TE Part #1410946-2
MULTI-GIG SOC. CAP SCREW, CUSTOMIZED HDW

TE Part #2-1614349-1
RN 0603 121K 0.1% 10PPM CUT LENGTH

Documents

Product Drawings

STM009M5CN = THRU-HOLE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1589488-6_S_c-1-1589488-6-s.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1589488-6_S_c-1-1589488-6-s.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1589488-6_S_c-1-1589488-6-s.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



1589488 Nanonics Cross Reference

English