



Connectors > PCB Connectors > Board-In Connectors > Paddle Board Connector



PCB Connector Assembly Type: **PCB Mount Paddleboard Connector**

PCB Mount Orientation: **Vertical**

Connector System: **Cable-to-Board**

Number of Positions: **4**

Centerline (Pitch): **1.27 mm [.05 in]**

[All Paddle Board Connector \(19\)](#)

Features

Electrical Characteristics

Operating Voltage	100 VDC
Insulation Resistance	1000 MΩ

Industry Standards

UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL E28476

Dimensions

Row-to-Row Spacing	2 mm[.059 in]
Compatible Insulation Diameter Range	.8 – 1 mm[.035 – .039 in]
Connector Height	5.1 mm[.2 in]
Wire Size	28 AWG
Connector Length	8.6 mm[.339 in]

Packaging Features

Packaging Quantity	2500
Packaging Method	Reel

Operation/Application

Solder Process Feature	Board Standoff
------------------------	----------------



Circuit Application	Signal
Contact Features	
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material Finish	Matte
Wire Contact Termination Area Plating Material	Tin
Wire Contact Termination Area Plating Material Finish	Matte
PCB Contact Termination Area Plating Material Thickness	3 – 5 µm[118.11 – 196.85 µin]
Contact Base Material	Phosphor Bronze
Wire Contact Termination Area Plating Thickness	1 µm[39.37 µin]
PCB Contact Termination Area Plating Material	Tin
Contact Current Rating (Max)	1.5 A
Mechanical Attachment	
PCB Mount Retention Type	Kinked Solder Tails
PCB Mount Alignment	With
PCB Mount Retention	With
Termination Features	
Rectangular Termination Post & Tail Width	.4 mm[.015 in]
Rectangular Termination Post & Tail Thickness	.5 mm[.02 in]
Termination Post & Tail Length	3.2 mm[.125 in]
Termination Method to PCB	Through Hole - Solder
Configuration Features	
Wire Entry Location	Top
PCB Mount Orientation	Vertical
Number of Positions	4
Compatible With Wire & Cable Type	Ribbon Cable
Number of Rows	2
Product Type Features	
PCB Connector Assembly Type	PCB Mount Paddleboard Connector
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board, Wire & Cable
Body Features	
Primary Product Color	Red



Housing Features

Centerline (Pitch)	1.27 mm[.05 in]
Housing Material	PBT GF

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts







TE Part # 677412-4
SEMI AUTO.MACHINE, MICRO-MATCH, 4-24 POS



TE Part # 2-438685-4
TERMINATION PUSHER




TE Part # 438685-1
TERM.PUSHER ASSY



TE Part # 734024-1
Micro-MaTch ADAPTER, 4-24 POS.

Also in the Series | Micro-MaTch Industrial



Board-In Connectors(20)



Connector Contacts(4)



Insertion & Extraction Tools(1)



Pluggable I/O Cable Assemblies(52)



Ribbon Cable Connectors(183)

Customers Also Bought




TE Part #CSI-UFFR-100-UFFR
U.FL/MHF1 to U.FL/MHF1 100mm 1.13 OD



TE Part #CSI-UFFR-200-UFFR
U.FL/MHF1 to U.FL/MHF1 200mm 1.13 OD



TE Part #1393224-7
RYA31005



TE Part #556881-2
RCPT ASY,VRT,AMPINRGY WTB,2POS



TE Part #2-1393224-6
RYA51005



TE Part #CAT-D799-H342
DEUTSCH DRC Headers



TE Part #214025-E
SRCP 1,27 4 F 1 I2426 137 * 162 1,07 TRA



TE Part #214038-E
SRCP 1,27 6 F 1 I2426 137 * 162 1,07 TRA



Documents

Product Drawings

MICRO-MATCH PBC.04P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_215570-4_S.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_215570-4_S.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_215570-4_S.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Micro-MaTch Catalog

English

Ribbon Cable Interconnect Solutions

English

Centerline Micro-Match Connector Series

English

Product Specifications

Application Specification

English

micro match miniature connector system

English