

# FLKM 50-PA-AB/1756/IN/EXTC - Front adapter



2302748

<https://www.phoenixcontact.com/us/products/2302748>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE front adapters, for Allen Bradley ControlLogix and Honeywell PlantScape, input card IB 32.

The front adapters are pushed into the high 1756-TBE hoods (not supplied as standard).

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 2302748             |
| Packing unit                         | 1 pc                |
| Minimum order quantity               | 1 pc                |
| Sales key                            | C421                |
| Product key                          | CK231S              |
| Catalog page                         | Page 470 (C-5-2019) |
| GTIN                                 | 4017918910471       |
| Weight per piece (including packing) | 65.333 g            |
| Weight per piece (excluding packing) | 62.7 g              |
| Customs tariff number                | 85369010            |
| Country of origin                    | DE                  |

# FLKM 50-PA-AB/1756/IN/EXTC - Front adapter



2302748

<https://www.phoenixcontact.com/us/products/2302748>

## Technical data

### Product properties

|                |               |
|----------------|---------------|
| Product type   | Front adapter |
| Product family | VARIOFACE     |

#### Insulation characteristics: Air clearances and creepage distances

|                      |                       |
|----------------------|-----------------------|
| Insulation           | Functional insulation |
| Overvoltage category | II                    |
| Pollution degree     | 2                     |

### Electrical properties

|                        |                       |
|------------------------|-----------------------|
| Operating voltage (AC) | ≤ 30 V AC             |
| Operating voltage (DC) | ≤ 60 V DC             |
| Nominal operating mode | 100% operating factor |
| Current (per branch)   | ≤ 1 A                 |

#### Air clearances and creepage distances

|                          |                    |
|--------------------------|--------------------|
| Rated insulation voltage | 63 V               |
| Rated surge voltage      | 0.6 kV (1.2/50 µs) |

#### Supported controller ALLEN-BRADLEY ControlLogix

|                   |           |
|-------------------|-----------|
| Suitable I/O card | 1756-IB32 |
|-------------------|-----------|

#### Supported controller HONEYWELL Experion PKS C200

|                   |            |
|-------------------|------------|
| Suitable I/O card | TC-IDD 321 |
|-------------------|------------|

### Connection data

#### Connection 1 (control level)

|                     |                    |
|---------------------|--------------------|
| Connection method   | Plug-in connection |
| Number of positions | 36                 |

#### Connection 2 (field level)

|                                  |                   |
|----------------------------------|-------------------|
| Connection in acc. with standard | IEC 60603-13      |
| Connection method                | IDC/FLK pin strip |
| Number of connections            | 1                 |
| Number of positions              | 50                |
| Insertion/withdrawal cycles      | > 50              |
| Pitch                            | 2.54 mm           |

#### Connection 3 (supply)

|                               |                      |
|-------------------------------|----------------------|
| Connection method             | Screw connection     |
| Stripping length              | 7 mm                 |
| Screw thread                  | M3                   |
| Number of positions           | 4                    |
| Conductor cross section rigid | 0.14 mm² ... 1.5 mm² |

# FLKM 50-PA-AB/1756/IN/EXTC - Front adapter



2302748

<https://www.phoenixcontact.com/us/products/2302748>

|   |  |
|---|--|
| Conductor cross-section rigid (2 conductors with same cross section)    | 0.08 mm <sup>2</sup> ... 0.5 mm <sup>2</sup>                                   |
| Conductor cross section flexible  | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>                                   |
|   | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (Ferrule without plastic sleeve)  |
|   | 0.25 mm <sup>2</sup> ... 0.75 mm <sup>2</sup> (Ferrule with plastic sleeve)    |
| Conductor cross section flexible (2 conductors with same cross section) | 0.08 mm <sup>2</sup> ... 0.75 mm <sup>2</sup>                                  |
|   | 0.25 mm <sup>2</sup> ... 0.34 mm <sup>2</sup> (Ferrule without plastic sleeve) |
|   | 0.5 mm <sup>2</sup> ... 0.5 mm <sup>2</sup> (TWIN ferrule with plastic sleeve) |
| Conductor cross section AWG   | 28 ... 16  |
| Tightening torque   | 0.22 Nm ... 0.25 Nm  |
| Pitch   | 3.81 mm  |

## Dimensions

### Item dimensions

|        |          |
|--------|----------|
| Width  | 104.9 mm |
| Height | 33 mm    |
| Depth  | 40.84 mm |

## Environmental and real-life conditions

### Ambient conditions

|  |                  |
|--|------------------|
| Degree of protection (Module)                | IP00             |
| Degree of protection (Installation location) | ≥ IP54           |
| Ambient temperature (operation)              | -20 °C ... 50 °C |
| Ambient temperature (storage/transport)      | -20 °C ... 70 °C |
| Altitude                                     | ≤ 2000 m         |

## Standards and regulations

### Air clearances and creepage distances

|                       |                |
|-----------------------|----------------|
| Standards/regulations | EN IEC 60664-1 |
|-----------------------|----------------|

## Mounting

|                   |                  |
|-------------------|------------------|
| Mounting type     | Plug-in mounting |
| Mounting position | any              |

## Notes

|                    |  |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|


## FLKM 50-PA-AB/1756/IN/EXTC - Front adapter



2302748

<https://www.phoenixcontact.com/us/products/2302748>

## Drawings



### Connection scheme FLKM 50-PA-AB/1756/IN/EXTC

# FLKM 50-PA-AB/1756/IN/EXTC - Front adapter



2302748

<https://www.phoenixcontact.com/us/products/2302748>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2302748>

| cUL Recognized<br>Approval ID: E238705 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|  | 125 V                 | 1 A                   | -                 | -                           |

| UL Recognized<br>Approval ID: E238705 |                       |                       |                   |                             |
|---------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|                                       | 125 V                 | 1 A                   | -                 | -                           |

| cULus Recognized |  |  |  |  |
|------------------|--|--|--|--|
|------------------|--|--|--|--|

# FLKM 50-PA-AB/1756/IN/EXTC - Front adapter



2302748

<https://www.phoenixcontact.com/us/products/2302748>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27242292 |
| ECLASS-12.0 | 27242292 |
| ECLASS-13.0 | 27242292 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002584 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 32151600 |
|-------------|----------|

## Environmental product compliance

## EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

## China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

## EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 51622aad-fd34-471e-8b78-18f128637d39 |