




Mini-SAS HD

TE Internal #: 2227640-1
Internal Mini-SAS HD, Receptacle, Cable-to-Board, 72 Position, 4 Row, 2 Port, Vertical, Through Hole - Press-Fit, Mini-SAS HD
[View on TE.com >](#)

Connectors > PCB Connectors > SAS & MiniSAS > Internal Mini-SAS HD Receptacles



SAS Connector Type: Internal Mini-SAS HD
Connector & Housing Type: Receptacle
Connector System: Cable-to-Board
Number of Positions: 72
Number of Rows: 4

[All Internal Mini-SAS HD Receptacles \(6\)](#)

Features

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Contact Features

Contact Underplating Material	Nickel
Contact Mating Area Plating Material	Gold
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin

Body Features

Primary Product Color	Black
-----------------------	-------

Mechanical Attachment

PCB Mount Retention Type	M2 Screw
PCB Mount Retention	With

Packaging Features

Packaging Method	Box & Tray
------------------	------------



Dimensions

Profile Height from PCB	14.2 mm[.559 in]
-------------------------	------------------

Usage Conditions

High Temperature Housing	Yes
Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]

Housing Features

Housing Material	LCP (Liquid Crystal Polymer)
Centerline (Pitch)	.75 mm[.029 in]

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Shell	Without
SAS Connector Type	Internal Mini-SAS HD
Connector & Housing Type	Receptacle
Connector System	Cable-to-Board

Configuration Features

Number of Positions	72
Number of Rows	4
Number of Ports	2
PCB Mount Orientation	Vertical

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
---------------------------	--------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2820333-4 C/A, INTERNAL HD MSAS, 100 OHM, STR-R/A	TE Part # 2820333-1 C/A, INTERNAL HD MSAS, 100 OHM, STR-R/A	TE Part # 2820338-1 C/A, INTERNAL HD MSAS, 100 OHM, STR, 8X	TE Part # 2820338-2 C/A, INTERNAL HD MSAS, 100 OHM, STR, 8X
 TE Part # 2820332-4 C/A, INTERNAL HD MSAS, 100 OHM, STR-R/A	 TE Part # 2820328-3 C/A, INTERNAL HD MINI SAS, 100 OHM, R/A	 TE Part # 2820350-3 C/A, INTERNAL HD MINI SAS, 100 OHM, STR	TE Part # 2820333-3 C/A, INTERNAL HD MSAS, 100 OHM, STR-R/A





TE Part # 2820329-1
C/A, INTERNAL HD MINI SAS, 100 OHM, R/A



TE Part # 2820350-4
C/A, INTERNAL HD MINI SAS, 100 OHM, STR



TE Part # 2820332-2
C/A, INTERNAL HD MSAS, 100 OHM, STR-R/A



TE Part # 2820328-2
C/A, INTERNAL HD MINI SAS, 100 OHM, R/A




TE Part # 2820328-4
C/A, INTERNAL HD MINI SAS, 100 OHM, R/A



TE Part # 2820332-1
C/A, INTERNAL HD MSAS, 100 OHM, STR-R/A



TE Part # 2820328-1
C/A, INTERNAL HD MINI SAS, 100 OHM, R/A



TE Part # 2820329-2
C/A, INTERNAL HD MINI SAS, 100 OHM, R/A



TE Part # 2820329-4
C/A, INTERNAL HD MINI SAS, 100 OHM, R/A



TE Part # 2820329-3
C/A, INTERNAL HD MINI SAS, 100 OHM, R/A



TE Part # 2820332-3
C/A, INTERNAL HD MSAS, 100 OHM, STR-R/A




TE Part # CAT-IN819-C76264
Internal Mini-SAS HD Receptacles

Also in the Series | Mini-SAS HD



Pluggable I/O Cable Assemblies(18)



Pluggable IO Connectors & Cages(10)



SAS & MiniSAS(10)



SATA & Micro SATA(1)

Customers Also Bought




TE Part #1473005-4
SEMI-HARD TRAY DDR2 SODIMM SOCKET 200P 5



TE Part #5352115-1
Z-PACK/C RAF 55P



TE Part #2110819-1
QSFP+ Enh EVERCLEAR PT Conn



TE Part #280370-2
2P AMPMODU II SHRD HDR, ST, 0.38 AU



TE Part #2310924-3
NRW FABRIC BOLSTER,P0, W/O COVER

TE Part #1734595-5
1.0 WTB SR VT HDR 5 POS

TE Part #2-382811-1
SHUNT, ECON, PHBRN, BLACK

TE Part #1982995-3
CROWN CLIP JUNIOR SCREW-MOUNT CONN

TE Part #5787973-2
36 POS .8MM CHAMP RCPT ASSY

TE Part #2149178-1
1xN SFP+ Heatsink Clip

Documents

Product Drawings

1X2 VERT ASSY, MINI SAS HD INTERNAL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2227640-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2227640-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2227640-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English