




PIDG

TE Internal #: 323975
Butt Splice, 24 – 20 AWG, .2 – .6 mm² Wire, Serrated, .32 – 1.29 kcmil, 320 – 1290 CMA, Copper, Natural, Length 26.29 mm [1.035 in], Loose Piece, PIDG

[View on TE.com >](#)

Terminals & Splices > Splices > PIDG Butt Splices



Splice Type: **Butt Splice**
Wire Size: **.2 – .6 mm²**
Sealable: **No**
Splice Features: **Serrated**

[All PIDG Butt Splices \(25\)](#)

Features

Packaging Features

Packaging Quantity	50
Packaging Method	Loose Piece

Contact Features

Military Part Class	Class I
Terminal Plating Material	Tin
Contact Base Material	Copper
Barrel Type	Closed

Body Features

Product Weight	.735 g
Insulation Material	Nylon
Splice Features	Serrated
Primary Product Color	Natural

Product Type Features



Splice Accessory Type	Splice
Splice Type	Butt Splice
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	.32 – 1.29 kcmil
Compatible Insulation Diameter Range	2.54 mm[.1 in]
Product Length	26.29 mm[1.035 in]

Usage Conditions

Insulation Option	Fully Insulated
-------------------	-----------------

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Splice	Yes
-----------------------------	-----

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 59275
T-HEAD PIDG PG SH 26-20 ASSY



TE Part # 46256
DAHT COAXIAL PIDG 24-20 ASSY



TE Part # 59300
T-HEAD PIDG PG 26-16 ASSY




TE Part # 47907-1
DAHT PIDG 24-20 ASSY

Also in the Series | PIDG



Compression Connectors(17)



Crimp Wire Pins, Tabs & Ferrules(41)



Hand Crimping Tools(2)




Knife Disconnects(11)



Quick Disconnects(38)



Ring Terminals(588)



Spade Terminals(228)



Special Purpose Terminals(1)




Splices(41)

Customers Also Bought




TE Part #895514-000
222K132-25-00-0




TE Part #556533-000
207W613-100-01/184-0




TE Part #1616083-2
A981K (FAA/PMA)=RELAY




TE Part #610026-000
D-305-04




TE Part #ZPF000000000007115
9602-04H 16-26 PN




TE Part #ZPF000000000007118
9602-04H 16-8 PN




TE Part #ZPF000000000009425
992 B6 KA 14S 5 SN 2



TE Part #ZPF000000000100562
992 B6 KA 28-12 PW 2



TE Part #ZPF000000000113240
992-00 KA 28-12 SW 2



TE Part #131435-3
KIT, CONNECTOR GROUNDING, 20 P

Documents

Product Drawings
SPLICE, BUTT, PIDG, 24-20
English

CAD Files
3D PDF
English
Customer View Model
ENG_CVM_323975_M.2d_dxf.zip



English

Customer View Model

[ENG_CVM_323975_M.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_323975_M.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[PIDG TERMINALS & SPLICES Quick Reference Guide](#)

English

Agency Approvals

[CSA Certificate](#)

English