




REVISIONS

1471-9 (3/13)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			




3-2834465-2
3-2480474-2





THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FRANK FAN 01MAR2021 CHR GEORGE FU 01MAR2021 APVD MING SHI 01MAR2021		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±0.25 3 PLC ±. 4 PLC ±. ANGLES ±.		NAME MINIDYNAMIC HEADER 1.8 MM PITCH SMT TYPE	
MATERIAL - -		APPLICATION SPEC - WEIGHT -		SIZE A2	CAGE CODE -
				DRAWING NO C-2834465	RESTRICTED TO -
		CUSTOMER DRAWING		SCALE 3:1	SHEET 2 of 4
				REV	C


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			






4-2834465-4
4-2480474-4



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FRANK FAN 01MAR2021		 TE Connectivity	
		CHK GEORGE FU 01MAR2021			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME MINIDYNAMIC HEADER 1.8 MM PITCH SMT TYPE	
mm		0 PLC ± 1 PLC ± 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±			
					
MATERIAL		FINISH			
-		-		SIZE	
-		-		CAGE CODE	
		WEIGHT		DRAWING NO	
		-		A2	
		CUSTOMER DRAWING		C-2834465	
				RESTRICTED TO	
				-	
				SCALE 3:1	
				SHEET 3 of 4	
				REV C	



NOTES:
1 PLEASE REFER DIMENSIONS AND REQUIREMENTS IN SHEET1 AND SHEET2.



5 5	4-2834499-4	4-2834465-4	4-2480475-4	4-2480474-4	72	250	750
	4-2834499-0	4-2834465-0	4-2480475-0	4-2480474-0	72	250	750
	3-2834499-6	3-2834465-6	3-2480475-6	3-2480474-6	72	250	750
	3-2834499-2	3-2834465-2	3-2480475-2	3-2480474-2	56	250	750
	2-2834499-8	2-2834465-8	2-2480475-8	2-2480474-8	56	250	750
	2-2834499-4	2-2834465-4	2-2480475-4	2-2480474-4	56	250	750
	2-2834499-0	2-2834465-0	2-2480475-0	2-2480474-0	44	250	1000
	1-2834499-6	1-2834465-6	1-2480475-6	1-2480474-6	44	250	1000
	1-2834499-2	1-2834465-2	1-2480475-2	1-2480474-2	44	250	1000
PN (Y KEY) TIN PLATING	PN (X KEY) TIN PLATING	PN (X KEY) GOLD PLATING	PN (Y KEY) GOLD PLATING	TAPE WIDTH (MM)	QUANTITY PER REEL /PCS	QUANTITY PER CARTON /PCS	

44 MM WIDTH TAPE AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FRANK FAN 01MAR2021 CHK GEORGE FU 01MAR2021 APVD MING SHI 01MAR2021		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±		NAME MINIDYNAMIC HEADER 1.8 MM PITCH SMT TYPE	
		PRODUCT SPEC 108-137443			
MATERIAL - -		APPLICATION SPEC - WEIGHT -		SIZE A2	CAGE CODE -
		CUSTOMER DRAWING		DRAWING NO C-2834465	RESTRICTED TO -
				SCALE 3:1	SHEET 4 of 4
				REV C	