




zQSFP+/QSFP28

TE Internal #: 2170805-5
QSFP28/56, Cage, Signal, Operating Temperature Range -40 – 85 °C [-40 – 185 °F], Data Rate (Max) 28 Gb/s, 2 Ports, Port Matrix Configuration 1 x 2

[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages



Form Factor: **QSFP28/56**
Pluggable I/O Product Type: **Cage**
Sealable: **No**
Circuit Application: **Signal**
Operating Temperature Range: **-40 – 85 °C [-40 – 185 °F]**

Features

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	2.05 mm[.081 in]

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
-----------------------------	------------------

Contact Features

PCB Contact Termination Area Plating Material	Tin
---	-----

Housing Features

Cage Material	Nickel Silver
---------------	---------------

Packaging Features

Packaging Method	Box & Tray
------------------	------------

Configuration Features



Number of Rear EONs per Port Column	1
Number of Ports	2
Port Matrix Configuration	1 x 2

Operation/Application

Pluggable I/O Applications	SFP+ Stacked Belly-to-Belly
Heat Sink Compatible	Yes
Circuit Application	Signal

Product Type Features

Cage Type	Ganged
Form Factor	QSFP28/56
Pluggable I/O Product Type	Cage
Sealable	No

Electrical Characteristics

Data Rate (Max)	28 Gb/s
-----------------	---------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Other

Included Lightpipe	No
EMI Containment Feature Type	Internal/External EMI Springs
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC




	Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1551920-2 zQSFP+ connector assembly	 TE Part # CAT-Q17-N490325 QSFP56 to QSFP56 Cable Assembly: 30 AWG	 TE Part # CAT-C11-N49 QSFP28-Two QSFP28 Cable Assembly: 30 AWG	 TE Part # CAT-C11-N490333 QSFP28-Four SFP+ Cable Assembly: 30 AWG
 TE Part # CAT-Q17-N490333 QSFP56-Four SFP56 Cable Assembly: 26 AWG	 TE Part # CAT-C11-N490325 QSFP28-Four SFP+ Cable Assembly: 26 AWG	 TE Part # CAT-Q17-N49011 QSFP56-Four SFP56 Cable Assembly: 30 AWG	 TE Part # CAT-C11-Z806726 QSFP28 to QSFP28 Cable Assembly: 30 AWG
 TE Part # CAT-C11-Q17 QSFP56 to QSFP56 Cable Assembly: 26 AWG	 TE Part # 1888810-2 EMI/Dust Cover,XFP And QSFP	 TE Part # CAT-Q17-N49033 QSFP56-Two QSFP56 Cable Assembly: 30 AWG	 TE Part # CAT-C11-Z8 QSFP28 to QSFP28 Cable Assembly: 26 AWG


Also in the Series | zQSFP+/QSFP28



Heat Sinks(7)



Pluggable I/O Cable Assemblies(78)



Pluggable IO Connectors & Cages(424)

Customers Also Bought



TE Part #1551920-2
zQSFP+ connector assembly



TE Part #9-1614882-9
CPF 0603 22R 0.1% 25PPM 1K RL



TE Part #2-1676480-2
CRG0402 1% 1K0



TE Part #4-1676480-3
CRG0402 1% 2K2



TE Part #3-1676480-7
CRG0402 1% 240R



TE Part #1982260-5
Z-PACK Slim UHD Power 5 pos pl

Documents

Product Drawings

CAGE ASSEMBLY, 1X2, QSFP28, SPRING

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2170805-5_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2170805-5_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2170805-5_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages
QSFP28/56 and zQSFP+ Interconnects

English

Product Specifications
Application Specification

English