




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **2**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-0**

Features

Packaging Features

Packaging Quantity	1000
--------------------	------

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Retention Type	Latch
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Product Type Features

Connector & Contact Terminates To	Wire & Cable
Sealable	No
Connector System	Wire-to-Board, Wire-to-Wire
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	2
---------------------	---



Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	With

Housing Features

Housing Material	Nylon
Centerline (Pitch)	15 mm[.59 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>








EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Melamine (3% in Component Part) Article Safe Usage Statements: Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 170330-2 PL 187 RECEPTACLE 24-20 AWG NPPHBZ	 TE Part # 2-174712-1 PL MK2 2P 187 HOUSING REC NATURAL	 TE Part # 170332-1 PL 187 RECEPTACLE 18-14 AWG PTPBR	 TE Part # 170326-5 187 PL MKII REC. 18-14AWG PTPB
 TE Part # 170324-1 187 PL MKII REC. 24-20AWG PTBR	 TE Part # 170326-1 187 PL MKII REC. 18-14AWG PTBR	 TE Part # 170324-2 PL 187 RECEPTACLE 24-20 AWG 0.3 NPCU	 TE Part # 170330-1 PL MKII 187 REC 24-20AWG PTBR LP
 TE Part # 170331-1 PL MKII 187 REC 20-16AWG PTBR LP	 TE Part # 170325-1 187 PL MKII REC. 20-16AWG PTBR	 TE Part # 170325-5 187 PL MKII REC. 20-16AWG PTBR	

Also in the Series | Positive Lock 187



Crimp Terminal Housings(86)



Insertion & Extraction Tools(2)



Insulation Boots & Sleeves(7)



Quick Disconnects(57)

Customers Also Bought



TE Part #179466-1
AMP POWER DBL LOCK CAP HSG 6P




TE Part #794761-1
09P UMNL CAP HSG WHITE,P/MT,V0




TE Part #794760-1
06P UMNL CAP HSG WHITE,PAN MNT



TE Part #63127-1
250 FASTON REC 22-18 AWG BR



TE Part #1-520935-1
250 HSG. PL MKII REC. 15.11mm 2P NAT



TE Part #353256-1
110 HSG. PL EX REC. 7.6mm 3P NAT



TE Part #5-177901-1
POWER DBL LOCK PLUG HSG 6P (GWT)



TE Part #3-1565081-4
GRACE INERTIA CONNECTOR 3.5 2P



TE Part #3-647449-1
SL156 RCPT,SPCL LUBE, LF



TE Part #520988-3
ULTRA-POD 250 ASSY REC 22-18 AWG TPBR

Documents

Product Drawings

POSITIVE LOCK 187 (4.8 MM) HOUSING

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_176498-1_F.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_176498-1_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_176498-1_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[FASTON Housings](#)

English

[Positive Lock Receptacles](#)

English

Agency Approvals

[UL Report](#)

English