


AMPLIMITE

TE Internal #: 1-1393738-2

TE Internal Description: V42254A6000K125=SUB D GEHAEUSE

[View on TE.com >](#)

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Perfluorohexane-1-sulphonic acid and its salts (.16% in Component part) <small>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1393738-3
V42254A6000K125=SUB D GEHAEUSE

Customers Also Bought



TE Part #1-1462038-6
IM06NS=IM RELAY 140mW 12V



TE Part #66102-8
III+ PIN,24-20,15AU/FL,STRIP



TE Part #1623214-1
CRG0805 1% 3K3



TE Part #1623173-1
CRG0805 1% 2K0



TE Part #2-2176343-5
CRGCQ 1206 1K0 1%




TE Part #2-1393561-9
V42254A 262V 19=SUB D SCHRAUBE




TE Part #5-2071571-8
SR4M4024



TE Part #413638-E
STVH15 15 M ZD VV 3-00 LAFD ** 199
E 17



TE Part #1-1393738-0
V42254A6000K109=SUB D GEHAEUSE



TE Part #1-1393738-3
V42254A6000K137=SUB D GEHAEUSE

Documents

Product Drawings

[V42254A6000K125=SUB D GEHAEUSE](#)

English

Instruction Sheets

[mounting guideline for d-Sub housings](#)

English

Instruction Sheet (U.S.)

English

1-1393738-2

V42254A6000K125=SUB D GEHAEUSE

