




Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Receptacle Frame**

Primary Product Color: **Black**

Primary Product Material: **Polycarbonate**

Operating Temperature (Max): **105 °C [221 °F]**

Operating Temperature Range: **-20 – 105 °C [-4 – 221 °F]**

Features

Dimensions

Product Width	25.8 mm
Product Length	48 mm[1.89 in]
Product Height	28.1 mm[1.11 in]

Packaging Features

Packaging Method	Package
Packaging Quantity	830

Product Type Features

Connector Hardware Accessory Type	Receptacle Frame
Hardware Accessory Function	Mounting

Body Features

Primary Product Color	Black
Primary Product Material	Polycarbonate

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-20 – 105 °C[-4 – 221 °F]



Other

EU RoHS Compliance	Compliant
--------------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Customers Also Bought



TE Part #1-5227079-6
COMM BNC PLUG



TE Part #1445957-2
HSG SUB ASY,BLACK



TE Part #1604081-1
HSG,2X3 PWR PROD PLUR W/O LATC



TE Part #1744042-1
L/P CONTACT,16-20AWG



TE Part #1623925-3
CFR100 5% 10K



TE Part #226990-1
RTANG JACK, BNC PCB

Documents

Product Drawings

HSG,2X3 POWER PROD RECPT

English

CAD Files

Customer View Model

ENG_CVM_CVM_1604078-1_B.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1604078-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1604078-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1

English

Product Specifications

Application Specification

English

Application Specification

English

1604078-1

Receptacle Frame, Black, Polycarbonate

