

**6339167-3**

✓ ACTIVE


**OEG Miniature Relay PCF**

TE Internal #: 6339167-3

RJ45 Connector, Multiple Ports, 1 x 4, Jack, Shielded, Cat 5, Standard - Latch Down, 8 Position, Standard Profile, OEG Miniature Relay PCF

[View on TE.com >](#)

Connectors &gt; Modular Jacks &amp; Plugs &gt; RJ45 Connectors

Modular Jack & Plug Interface Type: **RJ45**Port Configuration: **Multiple Ports**Port Matrix Configuration: **1 x 4**Modular Jacks & Plugs Products: **RJ Type Jacks & Plugs**Connector Contact Density: **Standard****Features****Other**

Shield Panel Ground Type	Wave panel grounds.
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

**Packaging Features**

Packaging Quantity	20
Packaging Method	Tray, Box & Tray

**Mechanical Attachment**

Panel Mount Feature	Without
Connector Mounting Type	Panel Mount

**Contact Features**

Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Current Rating (Max)	1 A
Contact Mating Area Plating Material	Gold

Contact Base Material	Phosphor Bronze
-----------------------	-----------------

Contact Mating Area Plating Material Thickness	1.3 $\mu\text{m}$ [51 $\mu\text{in}$ ]
--	--

### Body Features

Shield Plating Material	Nickel
-------------------------	--------

Shield Material	Copper Zinc Alloy
-----------------	-------------------

PCB Ground Tab Location	4.57 mm[.18 in]
-------------------------	-----------------

Modular Jack Latch Orientation	Standard - Latch Down
--------------------------------	-----------------------

Connector Profile	Standard
-------------------	----------

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Performance Category	Cat 5
----------------------	-------

### Operation/Application

Indicator Type	No Indicator
----------------	--------------

Shielded	Yes
----------	-----

Circuit Application	Signal
---------------------	--------

### Configuration Features

Number of PCB Ground Tabs	3
---------------------------	---

Number of Panel Ground Tabs	15
-----------------------------	----

Multiple Port Configuration	Ganged
-----------------------------	--------

Port Configuration	Multiple Ports
--------------------	----------------

Port Matrix Configuration	1 x 4
---------------------------	-------

Connector Contact Density	Standard
---------------------------	----------

Number of Positions	8
---------------------	---

Number of Loaded Positions	8
----------------------------	---

PCB Mount Orientation	Right Angle
-----------------------	-------------

### Product Type Features

Connector Product Type	Connector Assembly
------------------------	--------------------

Modular Jack & Plug Interface Type	RJ45
------------------------------------	------

Modular Jacks & Plugs Products	RJ Type Jacks & Plugs
--------------------------------	-----------------------

Modular Connector Style	Jack
-------------------------	------

Grounding Options	PCB and Panel Ground
-------------------	----------------------

Connector & Contact Terminates To	Printed Circuit Board
-----------------------------------	-----------------------

### Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	3.56 mm[.14 in]

### Housing Features

Mating Entry Location	Side
Centerline (Pitch)	1.02 mm[.04 in]
Housing Color	Black
Housing Material	PCT Polyester

### Dimensions

Connector Height	13.71 mm[.54 in]
------------------	------------------

### Usage Conditions

Operating Temperature Range	-40 – 60 °C[-40 – 140 °F]
-----------------------------	---------------------------

### Product Compliance


For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C








#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


## Compatible Parts



## Also in the Series | OEG Miniature Relay PCF



## Customers Also Bought





## Documents

### Product Drawings

[ASSY,SHLD,1X4,MJ,WAVE PNL](#)

English

---

### CAD Files

[3D PDF](#)

English

Customer View Model

[ENG\\_CVM\\_6339167-3\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_6339167-3\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_6339167-3\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Product Specifications

[Application Specification](#)

English