

CRGH0603J15K

✓ ACTIVE

Neohm | Neohm CRGH

TE Internal #: 1879495-2

Surface Mount Power Resistor, Thick Film, 0603, .2 W, 15K ohm, 5 %, ±100 ppm/°C, Solder, 2 Terminations, Height .45 mm [.018 in], Neohm CRGH

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Power Resistor**
Element Type: **Thick Film**
Package Size Code: **0603**
Power Rating: **.2 W**
Resistance Value: **15K Ω**

Features

Electrical Characteristics

Operating Voltage	50 V
Power Rating	.2 W
Resistance Value	15K Ω
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	5 %

Product Type Features

Resistor Type	Power Resistor
Element Type	Thick Film
Package Size Code	0603

Configuration Features

Number of Resistors	1
---------------------	---

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.45 mm[.018 in]
Product Length	1.6 mm[.063 in]
Product Width	.8 mm[.031 in]



Usage Conditions

Temperature Coefficient	±100 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

CRGH0603J15K

Surface Mount Power Resistor, Thick Film, 0603, .2 W, 15K ohm, 5 %, ±100 ppm/°C, Solder, 2 Terminations, Height .45 mm [.018 in], Neohm CRGH



TE Part # 1879513-1
CRGH1206 1% 10R 0.5W



TE Part # 3-1879523-9
CRGH2512 1% 24R9 2W



TE Part # 6-1879501-0
CRGH2512 5% 300R 2W



TE Part # 1-1879502-0
CRGH2512 5% 33K 2W



TE Part # 9-1879510-1
CRGH0805 1% 10K 0.33W

Also in the Series | Neohm CRGH



Surface Mount Resistors(3655)

Customers Also Bought



TE Part #2176055-1
RLP73V 2B R010 1% 1K RL



TE Part #2-2176156-5
TLM 1206 0.5W R030 1% 50PPM 5K RL



TE Part #7-1676480-0
CRG0402 1% 510K



TE Part #CAT-SIGH262
Signal Header



TE Part #1-953893-1
16/8W+4SC MQS REC HSG ASS




TE Part #214788-E
EPSVA KS GDM4 TL 6 3,8 SN *
STROMVERSORG



TE Part #354094-E
SMCB 16 M AB VV 7-03 CL * 0007 137
E004



TE Part #1802830-1
40W TH HEADER ASSY BLACK



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1879495-2_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1879495-2_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1879495-2_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

High Power Thick Film Chip Resistors

English