


**1-968325-3** ACTIVE**MQS**

TE Internal #: 1-968325-3

Shield, Black, PBT GF, 52 Position, -40 – 120 °C [-40 – 248 °F]

[View on TE.com >](#)

Connectors &gt; Automotive Connectors &gt; Automotive Connector Accessories &gt; Automotive Connector Caps &amp; Covers

Protection & Strain Relief Accessory Type: **Shield**Strain Relief: **Without**Primary Product Color: **Black**Primary Product Material: **PBT GF**Number of Positions: **52**

## Features

### Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

### Dimensions

Compatible Cable Bundle Diameter Range	15.2 mm[.598 in]
--	------------------

### Packaging Features

Packaging Method	Carton
Packaging Quantity	500

### Other

Serviceable	Yes
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

### Configuration Features

Compatible With Connector Code	A
Number of Positions	52

### Product Type Features

Sealable	No
Protection & Strain Relief Accessory Type	Shield

### Mechanical Attachment

Strain Relief	Without
---------------	---------

### Body Features

Primary Product Color	Black
Primary Product Material	PBT GF

### Usage Conditions

Operating Temperature (Max)	120 °C [248 °F]
Operating Temperature Range	-40 – 120 °C [-40 – 248 °F]

### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



## Customers Also Bought



## Documents

### Product Drawings

#### MQS ABDECKKAPPE 52P

English

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-968325-3\\_B.2d\\_dxf.zip](#)

English

### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-968325-3\\_B.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-968325-3\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Product Specifications**

**STEUERGERATESTECKER 134-POL. MICRO QUADLOCK SYSTEM JUNIOR POWER TIMER**

English

**Product Specification**

English