



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **2**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-2**

Features

Dimensions

Product Length	23.37 mm[.92 in]
----------------	------------------

Packaging Features

Packaging Quantity	1
Packaging Method	Carton

Body Features

Connector & Keying Code	C
Primary Product Color	Natural

Product Type Features

Sealable	No
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	2
---------------------	---

Contact Features

--	--



Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	With

Mechanical Attachment

Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon
Centerline (Pitch)	14.94 mm[.588 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 928673-1
187 FASTON HSG. REC. 9.5MM2P
NATURAL

TE Part # 2238173-3
250 FASTON,REC.,22-12 AWG,TPBR

TE Part # 2238196-3
FASTON 250 STD REC STR 18-14TPBR

Also in the Series | FASTON 250

Compression Connectors(4)

Crimp Terminal Housings(132)

Insertion & Extraction Tools(6)

Magnet Wire Terminals(1)

PCB Terminals(134)

Quick Disconnects(425)

Splices(4)

Customers Also Bought



TE Part #CAT-103156-WBHSM
Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156

TE Part #1-175102-1
AMP CT CRIMP REC CONTACT

TE Part #499252-7
060 STRAIN RELIEF A-L RCPT

TE Part #1-154719-0
PL 250 REC HSG 1P NYLON NAT

TE Part #926790-4
PL 250 FLAG REC 1-2.5 MM2 PTP CUZN30 F53

TE Part #172074-1
187 HSG. PLMKII REC. NAT

TE Part #927854-6
PL 250 REC TERMINAL 17-13 AWG PTPB

TE Part #1-1658621-1
60 NOVO MIL/CTR 15DP,LEAD FREE

TE Part #926319-1
PL 250 REC HSG 2P NYLON BLACK

Documents

Product Drawings
250 FASTON HSG. REC 14.9MM2P NATURAL
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_521069-1_F.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_521069-1_F.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_521069-1_F.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



FASTON Housings

English

Agency Approvals

UL Report

English