




Triad 01 Panel/PCB Connector

TE Internal #: 4-1437719-5

3 Position Circular Connector, Cable-to-Cable, Sealable, Signal, Panel Mount, Reverse Gender, Nickel, CuZn, PBT, Triad 01 Panel /PCB Connector

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors



Number of Positions: 3

Connector System: **Cable-to-Cable**

Sealable: **Yes**

Contact Current Rating (Max): **3 A**

Circuit Application: **Signal**

Features

Electrical Characteristics

Operating Voltage	60 VAC
-------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Dimensions

Assembly Length	25.9 mm
-----------------	---------

Packaging Features

Packaging Quantity	25
--------------------	----

Body Features

Environmental Protection Type	Sealed
Environmental Protection	With
Shell Plating Material	Nickel
Shell Base Material	CuZn
Circular Connector Insulation Material Type	PBT



Hermetically Sealed

No

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Cable-to-Cable
Sealable	Yes
Circular Connector Type	Plug
Shell Type	Metal

Configuration Features

Number of Positions	3
Number of Power Positions	0
Number of Signal Positions	3
Contacts Preloaded	Yes

Contact Features

Contact Current Rating (Max)	3 A
Reverse Gender	Yes
Contact Layout Arrangement	Circular
Circular Connector Contact Type	Pin

Mechanical Attachment

Connector Mounting Type	Panel Mount
Mating Retention	With

Usage Conditions

Operating Temperature Range	-40 – 80 °C[-40 – 176 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
Shielded	No

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------



EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (1.72% in Component Part) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Hand solderable with lead free solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Triad 01 Panel/PCB Connector



Standard Circular Connectors(24)


Customers Also Bought




TE Part #1-1437719-5  
T01-0550-P03-MALE PLUG  
CONNECTOR SOLDER




TE Part #2-1445093-4  
MICRO MNL HDR ASSY S/ROW AU LF



TE Part #6469002-1  
HM-ZD 4PR HDR 80P 5.2MM



TE Part #2-1445093-3  
MICRO MNL HDR ASSY S/ROW AU LF




TE Part #2-1445093-2  
MICRO MNL HDR ASSY S/ROW AU LF




TE Part #2-1445093-5  
MICRO MNL HDR ASSY S/ROW AU LF




TE Part #2376591-2  
250 FASTON PCB TAB TPBR



TE Part #214782-E  
EPSVA KS GDM4 EE 10 3,8 SN \*  
STROMVERSOR



TE Part #5-6450860-2  
MBXLE VERT RCPT 2P+24S+2P



TE Part #6450546-1  
MBXL VERT RCPT 4P+24S

Documents

Product Drawings

T01-0560-P03-MALE REC PANEL-PCB MOUNT RA

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_4-1437719-5\_A.2d\_dxf.zip



English

Customer View Model

[ENG\\_CVM\\_CVM\\_4-1437719-5\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_4-1437719-5\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[M8 / M12 Connector System Catalog](#)

English

Product Specifications

[Product Specification](#)

English