




Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Keying Plug**
Operating Temperature (Max): **105 °C [221 °F]**
Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**
Hardware Accessory Function: **Coding & Keying**
EU RoHS Compliance: **Compliant**

Features

Product Type Features

Connector Hardware Accessory Type	Keying Plug
Hardware Accessory Function	Coding & Keying

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JUNE 2024 (241)
Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1827863-6
DYNAMIC 1100D REC HSG X 32P
BLACK

Also in the Series | Dynamic 1000 Series




Connector Contacts(40)



Connector Hardware(3)



Insertion & Extraction Tools(2)



PCB Headers & Receptacles(169)




Power Contacts(9)



Rectangular Connector Housings(2)



Wire-to-Board Connector Assemblies & Housings(152)



Wire-to-Board Headers & Receptacles (169)

Customers Also Bought



TE Part #1-178288-6
DYNAMIC D3100 REC HSG 6P



TE Part #2119141-1
CCII D1000 M REC TAB 28-22 ASSY



TE Part #1-1827579-1
DYNAMIC 1500T REC HSG 3P X BLACK



TE Part #4-2271013-0
CELLO,PIN,96P,TH,RA,FG,DIP3.0,-BLACK



TE Part #1-1903131-6
DYNAMIC 1200D TAB HSG 12P P/M



TE Part #1-1903128-7
DYNAMIC 1100D TAB HSG 34P P/M




TE Part #4-2271908-0
CELLO,REC,48P,TH,V,FG,DIP3.0,-



TE Part #T1871002101-000
HB-LM-TOP



TE Part #T2030001040-000
CEM-4.0



TE Part #2229983-1
D1200-RITS RELAY BOARD ASSY 10 POSITION

Documents

Product Drawings

DYNAMIC D-1000 KEYING PLUG

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1939588-1_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1939588-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1939588-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.