



Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Cable Clamp**

Primary Product Material: **Carbon Steel**

Number of Positions: **14**

Thread Size: **4-40**

Packaging Method: **Bag**

Features

Dimensions

Product Width	16.66 mm[.656 in]
Product Length	53.98 mm[2.125 in]
Product Height	31.75 mm[1.25 in]

Body Features

Cable Exit Angle	90°, 180°
Primary Product Plating Material	Nickel
Primary Product Material	Carbon Steel

Product Type Features

Strain Relief Accessory Type	Cable Clamp
------------------------------	-------------

Configuration Features

Number of Positions	14
---------------------	----

Mechanical Attachment

Thread Size	4-40
-------------	------

Usage Conditions

--	--



Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Method	Bag
Packaging Quantity	1

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Also in the Series | AMP M Series



Board-to-Board Jumpers & Shunts(5)



Connector Caps & Covers(11)



Connector Hardware(18)



Connector Strain Relief(11)




Rack & Panel Connectors(1)



Rectangular Power Connectors(54)

Customers Also Bought




TE Part #201298-1
FEMALE BLOCK 14 PL.



TE Part #66255-8
MALE CONTACT ASSY. (STRIP)



TE Part #2232983-1
EP 2.5 LIF RCPT CONTACT, 24-20 AWG



TE Part #1SNK150000R0000
MC612




TE Part #201922-1
SERIES M LOCKING SPRING CATCH



TE Part #1SNA115259R0600
M4/6.1



TE Part #1SNA235734R0000
RIB1-B



TE Part #1SNA115413R0100
MB6/8.L2



TE Part #5052842057
RNF-100-3/64-BK-STK



TE Part #3-1617004-3
B07D912BC1-0359 = RELAY.

Documents



Product Drawings

STRAIN RELIEF CLAMP (14) POS.

English

CAD Files

Customer View Model

ENG_CVM_201843-1_G.3d_igs.zip

English

Customer View Model

ENG_CVM_201843-1_G.3d_stp.zip

English

Customer View Model

ENG_CVM_201843-1_G.2d_dxf.zip

English

3D PDF

English

Customer View Model

ENG_CVM_CVM_201843-1_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_201843-1_H.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_201843-1_H.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M_SERIES_PIN_AND_SOCKET_CONNECTORS

English

Instruction Sheets

Instruction Sheet (U.S.)

English

STRAIN RELIEF CLAMP CATALOG NO. 201843 & 201844 FOR SERIES "M" CON

English

Agency Approvals

Agency Approval Document

English