

5-520314-8  ACTIVE

TRIO-MATE

TE Internal #: 5-520314-8

Connector Assembly, Wire-to-Board, 8 Position, 2.54 mm [.1 in]
Centerline, 1 Row, Right Angle, Socket, Tray, TRIO-MATE, FFC
Connectors

[View on TE.com >](#)



Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > FFC Connectors



FFC Connector Product Type: **Connector Assembly**

Connector System: **Wire-to-Board**

Number of Positions: **8**

Centerline (Pitch): **2.54 mm [.1 in]**

Number of Rows: **1**

Features

Industry Standards

UL Flammability Rating

UL 94V-0

Termination Features

Termination Method to PCB

Through Hole - Solder

Termination Post & Tail Length

2.54 mm [.1 in]

Electrical Characteristics

Operating Voltage

250 VAC

Insulation Resistance

5000 MΩ

Dielectric Withstanding Voltage (Max)

1400 VAC

Dimensions

PCB Thickness (Recommended)

1.57 mm [.062 in]

Operation/Application

Circuit Application

Signal

Mechanical Attachment

Mating Alignment Type

Polarization

PCB Mount Retention Type

Z Bend

PCB Mount Retention

With

Mating Retention

Without

Mating Alignment

With

Panel Mount Feature	Without
Connector Mounting Type	Board Mount
Packaging Features	
Packaging Quantity	660
Packaging Method	Tray
Contact Features	
Contact Mating Area Plating Material	Tin-Lead
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material Finish	Matte
Contact Type	Socket
Contact Current Rating (Max)	1 A
Housing Features	
Housing Material	Thermoplastic
Centerline (Pitch)	2.54 mm [.1 in]
FFC Cable Entry	Right Angle
Product Type Features	
Connector & Contact Terminates To	Printed Circuit Board
Connector & Housing Type	Receptacle
FFC Connector Product Type	Connector Assembly
Connector System	Wire-to-Board
Insertion Force Type	Low Insertion Force (LIF)
Configuration Features	
Number of Positions	8
Number of Rows	1
PCB Mount Orientation	Right Angle
Body Features	
Primary Product Color	Black
Usage Conditions	
Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
Other	
EU RoHS Compliance	Compliant

EU ELV Compliance

Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | [TRIO-MATE](#)



Customers Also Bought



Documents

Product Drawings

TRIOMATE ASSY H 8P L=2.54 LDFR

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_5-520314-8_Y.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-520314-8_Y.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-520314-8_Y.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Trio-Mate Flat Flexible Discrete Circuit .100 Connectors

English

[Application Specification](#)

Japanese

[Application Specification](#)

English