

Mini-SAS HD

TE Internal #: 2198484-1

Mini-SAS HD, Receptacle Assembly, .03mm [.75in] Centerline,
Signal, Operating Temperature Range -55 – 85 °C [-67 – 185 °F],
Data Rate (Max) 12 Gb/s

[View on TE.com >](#)



Connectors > Pluggable IO Connectors & Cages > Mini-SAS HD Cages



Form Factor: **Mini-SAS HD**
Pluggable I/O Product Type: **Receptacle Assembly**
Centerline (Pitch): **.03 mm [.75 in]**
Circuit Application: **Signal**
Operating Temperature Range: **-55 – 85 °C [-67 – 185 °F]**

[All Mini-SAS HD Cages \(11\)](#)

Features

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Contact Features

Contact Base Material	Copper Alloy
-----------------------	--------------

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	1.64 mm[.065 in]

Packaging Features

Packaging Method	Box & Tray
------------------	------------

Dimensions

PCB Thickness (Recommended)	.97 mm[.038 in]
Profile Height from PCB	16.44 mm[.647 in]

Housing Features



Housing Material	LCP (Liquid Crystal Polymer)
Centerline (Pitch)	.03 mm[.75 in]

Product Type Features

Form Factor	Mini-SAS HD
Pluggable I/O Product Type	Receptacle Assembly

Configuration Features

Number of Positions	36
Number of Ports	1
Port Matrix Configuration	1 x 1

Electrical Characteristics

Data Rate (Max)	12 Gb/s
-----------------	---------

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Other

Included Lightpipe	Yes
EMI Containment Feature Type	Internal/External EMI Springs
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>






EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 2337815-1 MINISAS HD TO MINISAS HD,30AWG, 0.5M	 TE Part # 2337815-3 MINISAS HD TO MINISAS HD,30AWG, 2M	 TE Part # 4-2337815-5 MINISAS HD TO MINISAS HD,28AWG, 4M	 TE Part # 4-2337815-3 MINISAS HD TO MINISAS HD,28AWG, 2M
 TE Part # 2337815-2 MINISAS HD TO MINISAS HD,30AWG, 1M	 TE Part # 4-2337815-6 MINISAS HD TO MINISAS HD,28AWG, 5M	 TE Part # 4-2337815-8 MINISAS HD TO MINISAS HD,28AWG, 7M	 TE Part # 2-2337815-4 MINISAS HD TO MINISAS HD,30AWG, 3M
 TE Part # 2-2337815-5 MINISAS HD TO MINISAS HD,30AWG, 4M	 TE Part # 2-2337815-1 MINISAS HD TO MINISAS HD,30AWG, 0.5M	 TE Part # 2337815-4 MINISAS HD TO MINISAS HD,30AWG, 3M	 TE Part # 4-2337815-7 MINISAS HD TO MINISAS HD,28AWG, 6M






TE Part # 4-2337815-2
MINISAS HD TO MINISAS HD,28AWG,
1M




TE Part # 4-2337815-4
MINISAS HD TO MINISAS HD,28AWG,
3M




TE Part # 4-2337815-1
MINISAS HD TO MINISAS HD,28AWG,
0.5M



TE Part # 2-2337815-3
MINISAS HD TO MINISAS HD,30AWG,
2M



TE Part # 2-2337815-2
MINISAS HD TO MINISAS HD,30AWG,
1M



TE Part # 2-2337815-6
MINISAS HD TO MINISAS HD,30AWG,
5M


Also in the Series | Mini-SAS HD



Mini-SAS Cages(10)



Pluggable I/O Cable Assemblies(18)




Pluggable IO Connectors & Cages(10)

Customers Also Bought



TE Part #499252-3
026 STRAIN RELIEF A-L RCPT



TE Part #2301826-2
AMPL PLUG HD20, VERT, 9P, B/L,4-40
S/LOC




TE Part #1658622-6
26 NOVO MIL/CTR 30DP,LEAD FREE




TE Part #CAT-CAPS0069
Compact String Pot, User Select
Output




TE Part #1437622-3
KLN700B1/4=KNOB KNURL W/IND LI




TE Part #1SNA115116R0700
M4/6



TE Part #1SNA115118R1100
M6/8



TE Part #1SNA165114R1700
M6/8.P



Documents

Product Drawings

MiniSAS HD 1x1 Rec Assy w/ LP

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2198484-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2198484-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2198484-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

7-1773461-9_MINI_SAS_HD_INTERCONNECT

English

Product Specifications

Application Specification

English

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English