




Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > FFC Connectors > FFC Receptacle Housing: 1.27mm



FFC Connector Product Type: **Housing**

Connector System: **Wire-to-Board**

Number of Positions: **24**

Centerline (Pitch): **1.27 mm [.05 in]**

Number of Rows: **2**

[All FFC Receptacle Housing: 1.27mm \(52\)](#)

Features

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
--------------------	----------------

Electrical Characteristics

Operating Voltage	100 VAC
Insulation Resistance	5000 MΩ
Dielectric Withstanding Voltage (Max)	300 VAC

Operation/Application

Circuit Application	Signal
---------------------	--------

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Retention Type	Latch
Mating Retention	With



Mating Alignment	With
Panel Mount Feature	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Packaging Features

Packaging Quantity	500
Packaging Method	Package

Housing Features

Housing Material	Polyester
Centerline (Pitch)	1.27 mm[.05 in]
FFC Cable Entry	Straight

Product Type Features

Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Receptacle
FFC Connector Product Type	Housing
Connector System	Wire-to-Board
Insertion Force Type	Normal

Configuration Features

Number of Positions	24
Number of Rows	2

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Type	Socket
--------------	--------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 1-104477-0
24 SYSTEM 50 HDR DRRA SHRD



TE Part # 104549-3
24 SYS50 SURFMNT HDR DRST SHRD



TE Part # 6-104666-0
24 SYSTEM 50 VERT SHRD HDR SN




TE Part # 6-104069-2
24 sys 50 hdr drra shrd sn




TE Part # 1-104068-1
24 SYSTEM 50 HDR DRST SHRD



TE Part # 1-104666-0
24 SYSTEM 50 VERT SHRD HDR



TE Part # CAT-F439-S01339127
1.27mm FFC Connectors Socket Contacts



TE Part # 6-104068-1
24 SYSTEM 50 HDR DRST SHRD



TE Part # 1-104069-2
24 SYSTEM 50 HDR DRRA SHRD

TE Part # 5-147377-9
24 SYS50 SMT HDR DR SHD SN

TE Part # 147377-9
24 SYS50 SMT HDR DR SHD W/O HD

TE Part # 5-104549-3
24 SYS50 S/M HDR DRST SHRDSN

TE Part # 6-104477-0
24 SYSTEM 50 HDR DRRA SHRD SN

TE Part # 5-104118-8
24 SYS 50 HDR DRRA UNSHRD SN

TE Part # 104068-1
20 SYSTEM 50 HDR DRST SHRD

Customers Also Bought

TE Part #35345
TERMINAL,PIDG R 12-10 1/4

TE Part #CAT-F439-R2435127
FFC Receptacle Housing: 1.27mm

TE Part #CAT-F439-R2435254
2.54mm FFC Connectors Receptacle Housing

TE Part #1-523725-0
ANVIL CM7398

Documents

Product Drawings

024 HOUSING FFC 50CL DR LATCH

English

CAD Files

Customer View Model

ENG_CVM_CVM_2-487937-4_R.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-487937-4_R.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-487937-4_R.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages

AMPMODU_INTERCONNECTION_SYSTEM_SECTION3AND4

English

Product Specifications

Application Specification

English

Application Specification

English

Agency Approvals

CSA Certificate

English