



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Terminal Orientation: **Straight**

Contact Base Material: **Steel**

Features

Industry Standards

Compatible With Agency/Standards Products	UL, CSA
---	---------

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	Without
Mating Retention Type	Dimple

Dimensions

Product Length	16.13 mm[.635 in]
Terminal Material Thickness	.3 mm[.012 in]

Packaging Features

--	--



Packaging Quantity	1000
Packaging Method	Loose Piece/Carton

Product Type Features

Insertion Force	Normal
-----------------	--------

Contact Features

Quick Disconnect Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Steel
Terminal Plating Material	Nickel
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 250 °C[-40 – 482 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 60006-1
250 FASTON TAB 18-14 AWG BR

TE Part # 63771-1
187 FASTON TAB NPST

TE Part # 60006-2
250 FASTON TAB 18-14 AWG TPBR

TE Part # 626417-2
250 FASTON REC 22-18 AWG TPBR

TE Part # 61960-1
187 FASTON TAB NPST

TE Part # 41778
250 FASTON TAB 18-14 AWG TPBR

TE Part # 63402-3
312 FASTON TAB BR


TE Part # 63402-2
312 FASTON TAB NPST

TE Part # 63953-1
187 FASTON TAB

Also in the Series | **FASTON 250**




Compression Connectors(4)



Crimp Terminal Housings(132)



Insertion & Extraction Tools(6)



Magnet Wire Terminals(1)



PCB Terminals(134)




Quick Disconnects(425)




Splices(4)


Customers Also Bought




TE Part #188834-1
Z-PACK/A M-HDR 154P.



TE Part #55654-1
TERMINAL R 90 DEG PG 8 10



TE Part #5746613-2
14 DIP PLUG CONN-W/COVER



TE Part #0641-3-1231L
CONT PIN



TE Part #130660
PIDG RING NYL




TE Part #NB14912001
DWP-125-3/4-0-STK




TE Part #176819-000
B-150-11



TE Part #163563-000
B-151-07



TE Part #41974
SPLICE 1000-3200 CMA BR



TE Part #1SNA198549R0500
FEH9-BE

Document



Product Drawings

250 FASTON TAB NPST

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_42559-1_N.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_42559-1_N.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_42559-1_N.3d_stp.zip

English

Customer View Model

ENG_CVM_42559-1_F1.3d_igs.zip

English

Customer View Model

ENG_CVM_42559-1_F1.3d_stp.zip

English

Customer View Model

ENG_CVM_42559-1_F1.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FASTON Tabs

English

Product Specifications

Product Specification

English

Agency Approvals

CSA Certificate

English

CSA Certificate

English