

REVISIONS					
P	LTR	DESCRIPTION		DATE	APVD
	J1	REVISED PER ECN-24-273904		24JUL2024	PS

OBSOLETE

1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.

2. ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY UNLESS OTHERWISE SPECIFIED.

3. MATERIAL:  
HOUSING - POLYPHENYLENE OXIDE (BLACK)  
TERMINALS - BERYLLIUM COPPER PLATED WITH EITHER .000030 [0.76µm] MIN GOLD OR GOLD FLASH OVER PALLADIUM NICKEL .000030 [0.76µm] MIN TOTAL, IN LOCALIZED GOLD PLATED AREA. .000050 [1.27µm] MIN NICKEL UNDERPLATE OVER ENTIRE TERMINAL.







4. WIRE SIZE: 22 AWG SOLID OR 22 AWG 7 STRANDS OF COPPER CONDUCTORS. MAX INSULATION DIAMETER OF .045 IS ACCEPTABLE FOR MOST APPLICATIONS.

5. CORING MAY OR MAY NOT APPEAR AND IS AT THE DISCRETION OF TYCO ELECTRONICS.

6. DIMENSIONS IN BRACKETS [ ] ARE MILLIMETERS.

H:\Zach Ream\Millhimes\ECR-06-026488\_ECD-06-026525\custc

OBSOLETE	AS SHOWN	552320-1
	DESCRIPTION	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. BUTNER 5-3-90	 TE Connectivity					
		CHK A. HOLT 5-15-90						
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME  PLUG ASSY, 64 POSITIONS, C SLOT BAIL LOCK, CHAMP-LOK				
		0 PLC ± - 						
		1 PLC ± - 						
		APVD J. TRAMNELL 5-17-90	PRODUCT SPEC					
		APPLICATION SPEC						
MATERIAL 	FINISH 	WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
		—		A2	00779	C=552320	—	
CUSTOMER DRAWING						SCALE	SHEET	REV
						NTS	1 of 1	J1