




PIDG

TE Internal #: 151439

Closed Ring Tongue Terminal, 24 – 22 AWG, #6 / M3.5 Stud, 3.6 mm [.142 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, PIDG

[View on TE.com >](#)

Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 509 – 810 CMA

Stud Size: #6, M3.5

Features

Configuration Features

Number of Holes	1
-----------------	---

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Body Features

Product Weight	.706 g
Insulation Sleeve Color	Black
Stripe Color	Black

Packaging Features

Packaging Quantity	500
Packaging Method	Box

Product Type Features



Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#6, M3.5
Sealable	No
Wire Insulation Support Retention Type	Non-Insulation Support

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Dimensions

Wire Size	509 – 810 CMA
Stud Diameter	3.6 mm[.142 in]
Tongue Thickness	.79 mm[.031 in]
Product Length	19.98 mm[.79 in]
Compatible Insulation Diameter (Max)	2.54 mm[.1 in]
Compatible Insulation Diameter Range	.89 – 2.54 mm[.035 – .1 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241)



	Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 69692-1
T-HEAD PIDG STRATO 26-20 ASSY




TE Part # 576778
HHHT PIDG PEEK STRATO 24-22 ASSY

Also in the Series | PIDG



Compression Connectors(17)



Crimp Wire Pins, Tabs & Ferrules(41)



Hand Crimping Tools(2)



Knife Disconnects(11)



Quick Disconnects(38)



Ring Terminals(588)



Spade Terminals(228)



Special Purpose Terminals(1)



Splices(41)

Customers Also Bought



TE Part #152895
20 PIDG RT NO 6 STUD PURPL



TE Part #1577620-1
TERMINAL RT PIDG PEEK STRATO 24-22 AWG



TE Part #2180143008
55A0811-20-9



TE Part #2180013004
55A0811-22-9




TE Part #2180263004
55A0811-18-9

TE Part #1616109-1
A700AAP (FAA/PMA)=RELAY



TE Part #ZPF000000000007069
951-1H 12-10 P 50



TE Part #CQ05573001
55A0811-12-9CK5050

TE Part #ER6594-000
D-436-83CS9376

TE Part #2-1616126-2

Documents



Product Drawings

PIDG 22 RING #6

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_151439_H.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_151439_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_151439_H.3d_stp.zip

English

Customer View Model

ENG_CVM_151439_O2.3d_igs.zip

English

Customer View Model

ENG_CVM_151439_O2.3d_stp.zip

English

Customer View Model

ENG_CVM_151439_O2.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.