

**2106056-8**

✓ ACTIVE


**SlimSeal | SlimSeal Connectors Headers**

TE Internal #: 2106056-8

Wire-to-Wire, 4 Position, .14 mm [3.5 in] Centerline, Sealable,  
Printed Circuit Board, SlimSeal Connectors Headers, Plug & Socket  
Lighting Connectors

[View on TE.com >](#)

Connectors &gt; Lighting Connectors &gt; Plug &amp; Socket Lighting Connectors

Connector System: **Wire-to-Wire**Number of Positions: **4**Centerline (Pitch): **.14 mm [ 3.5 in ]**Sealable: **Yes**Connector & Contact Terminates To: **Printed Circuit Board****Features****Body Features**

Primary Product Color	Black
-----------------------	-------

**Product Type Features**

Connector System	Wire-to-Wire
------------------	--------------

Sealable	Yes
----------	-----

Connector & Contact Terminates To	Printed Circuit Board
-----------------------------------	-----------------------

Lighting Connector Style	Receptacle
--------------------------	------------

**Configuration Features**

Number of Positions	4
---------------------	---

**Electrical Characteristics**

Operating Voltage	250 VDC
-------------------	---------

**Contact Features**

Contact Current Rating (Max)	5 A
------------------------------	-----

**Housing Features**

Centerline (Pitch)

.14 mm[3.5 in]

**Usage Conditions**

Operating Temperature Range

-40 – 105 °C[-40 – 221 °F]

**Other**

EU RoHS Compliance

Compliant

EU ELV Compliance

Compliant

**Product Compliance**For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2024  
(241)Candidate List Declared Against: JUNE  
2024 (241)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per  
homogenous material. Also BFR/CFR/PVC  
Free

Solder Process Capability

Reflow solder capable to 260°C

## Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

**Compatible Parts**



TE Part # 2106135-4  
Assembly, Free Hanging Plug, SLC, 4 pos

## Also in the Series | SlimSeal Connectors Headers



Plug & Socket Lighting Connectors(19)

## Customers Also Bought



TE Part #5747845-4  
15 MSFL RCPT RA 318 (IN,FM,BL)




TE Part #5536385-5  
ASSY,PIN,EUROCARD,TYPE B,LEAD-



TE Part #4-794627-2  
12P MICRO MNL ASSY,RA,SMT,LF



TE Part #4-794628-0  
10P MICRO MNL ASSY,R/A,SMT LF



TE Part #747080-2  
LATCH BLOCK/PACKAGED/.090 PANL



TE Part #2106135-4  
Assembly, Free Hanging Plug, SLC, 4 pos



TE Part #1-2106123-1  
CONTACT,Recept, SLC, Tin Plated, On Stri



TE Part #5-2301994-8  
RJ45 JACK INT.MAG. 10/100 LED 1X1 INV.



TE Part #627365-000  
TTMS-12.7-0



TE Part #5053192266  
RNF-100-1/2-BK-STK

## Documents

### Product Drawings

[Assembly, Right Angle SMT Header, 4-Posi](#)

English

---

### CAD Files

[3D PDF](#)

3D

[Customer View Model](#)

[ENG\\_CVM\\_CVM\\_2106056-8\\_B\\_c-2106056-8-b.2d\\_dxf.zip](#)

English

[Customer View Model](#)

[ENG\\_CVM\\_CVM\\_2106056-8\\_B\\_c-2106056-8-b.3d\\_igs.zip](#)

English

[Customer View Model](#)

[ENG\\_CVM\\_CVM\\_2106056-8\\_B\\_c-2106056-8-b.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[SLIMSEAL\\_SSL\\_CONNCOOTS](#)

English

---

### Product Specifications

[Application Specification](#)

English

---

### Agency Approvals

[UL Report](#)

English