


3-1718230-1

✓ ACTIVE

TE Internal #: 3-1718230-1

7 Position Housing, Housing for Male Terminals, Wire-to-Wire,
Sealable, Green, Wire & Cable, Power, Cable Mount (Free-Hanging)[View on TE.com >](#)

Connectors > Automotive Connectors > Automotive Housings > Circular DIN Housings



Number of Positions: 7

Connector & Housing Type: Housing for Male Terminals

Mating Pin Diameter: 1.5 mm [.059 in]

Connector System: Wire-to-Wire

Sealable: Yes

[All Circular DIN Housings \(64\)](#)

Features

Housing Features

Housing Material	PBT GF
------------------	--------

Industry Standards

IP Rating	IP69K
-----------	-------

UL Flammability Rating	UL 94HB
------------------------	---------

Dimensions

Product Length	44 mm[1.73 in]
----------------	----------------

Connector Height	28 mm[1.1 in]
------------------	---------------

Packaging Features

Packaging Method	Box
------------------	-----

Packaging Quantity	450
--------------------	-----

Mechanical Attachment

Strain Relief	Without
---------------	---------

Terminal Position Assurance	No
-----------------------------	----

Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Other

Serviceable	Yes
Connector Position Assurance Capable	No
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Body Features

Cable Exit Angle	180°
Primary Product Color	Green
Connector & Keying Code	C

Contact Features

Contact Size	1.5mm
Contact Type	Pin
Mating Pin Diameter	1.5 mm[.059 in]

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Circular
Connector & Housing Type	Housing for Male Terminals
Connector System	Wire-to-Wire
Sealable	Yes
Primary Locking Feature	Integrated in Housing
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	7
---------------------	---

Electrical Characteristics

Nominal Voltage Architecture	24 V, 42 V, 12 V, 48 V
------------------------------	------------------------

Usage Conditions

Operating Temperature (Max)	120 °C[248 °F]
Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]

Operation/Application

Circuit Application

Power

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 828922-1
2,5MM CAVITY PLUG FOR 5,4MM DI



TE Part # CAT-R7602-T273
ROUND CONNECTOR SYSTEM, PIN AND SOCKET




TE Part # CAT-C4962-B128
Circular DIN Backshells



TE Part # 185792-1
180 DEG CAP FOR CORRUGTD TUBE



Customers Also Bought



Documents

Product Drawings

[1,5MM PIN HSG 5-7 POS ASSY](#)

English

CAD Files

[3D PDF](#)

3D

[Customer View Model](#)

[ENG_CVM_CVM_3-1718230-1_A.2d_dxf.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_3-1718230-1_A.3d_igs.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_3-1718230-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English