




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **.34 – 1.5 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	Without
Mating Retention Type	Dimple

Packaging Features

Packaging Quantity	3000
Packaging Method	Strip/Reel

Dimensions

Product Length	37.78 mm[1.48 in]
----------------	-------------------



Terminal Material Thickness	.81 mm[.032 in]
Wire Size	.34 – 1.5 mm²

Product Type Features

Insertion Force	Normal
-----------------	--------

Contact Features

Quick Disconnect Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Steel
Terminal Plating Material	Nickel
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 250 °C[-40 – 482 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 61367-3

250 FASTON TAB 18-14 AWG TPBR

Also in the Series | FASTON 250

Compression Connectors(4)

Crimp Terminal Housings(132)

Insertion & Extraction Tools(6)

Magnet Wire Terminals(1)

PCB Terminals(134)

Quick Disconnects(425)

Splices(4)

Customers Also Bought



TE Part #1623730-8
BCHE 4 W 1R5 10%




TE Part #1-2308272-3
CABLE CLAMP3 (CASE RAW)



TE Part #1622960-1
CRG0603 1% 4K7



TE Part #5-1879338-6
CPF 0603 100K 1% 50PPM 1K RL



TE Part #1-2176083-0
EP 5W (S) 330R 5%



TE Part #1-2176339-3
CRGCQ 0603 100R 1%




TE Part #2176339-1
CRGCQ 0603 10R 1%



TE Part #5-1676480-0
CRG0402 1% 330R



TE Part #1-2308265-5
QL SET FOR VARIANT B 5



TE Part #6-2176558-1
3430 B2 1% 300R 100ppm 1k RL

Documents

Product Drawings

250 FASTON,TAB,22-15 AWG,NPST

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1217006-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1217006-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1217006-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



FASTON Tabs

English

Product Specifications

Application Specification

English