



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.51 – 1.31 mm²**

Mating Tab Width: **4.75 mm [.187 in]**

Mating Tab Thickness: **.51 mm [.02 in]**

Features

Industry Standards

Compatible With Agency/Standards Products	UL, CSA
---	---------

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Packaging Features

Packaging Quantity	9000
Packaging Method	Strip/Reel

Dimensions

Product Length	16.6 mm[.653 in]
----------------	------------------



Compatible Insulation Diameter Range	2.29 – 3.3 mm[.09 – .13 in]
Terminal Material Thickness	.3 mm[.012 in]
Wire Size	.51 – 1.31 mm²

Product Type Features

Insertion Force	Normal
-----------------	--------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2150007-1 OCEAN_2.0_Applicator-E-090F140F-REM	TE Part # 755336-1 DAHT FASTON 22-14 ASSY	TE Part # 2178549-2 187 FASTON,REC.,18-14 AWG,TPBR	TE Part # 2232975-1 187 FASTON,REC.,20-16 AWG,TPBR
TE Part # 2150007-2 OCEAN_2.0_Applicator-E-090F140F-REA	TE Part # 7-2150007-7 OCEAN_2.0_SPARE_PART_KIT-090F140F		

Also in the Series | FASTON 187

Crimp Terminal Housings(41)	Insertion & Extraction Tools(1)	Joints & Splices(1)	PCB Terminals(42)
------------------------------------	--	--------------------------------	--------------------------



Quick Disconnects(207)



Splices(1)

Customers Also Bought




TE Part #440129-7
2.0MM,HSG,7POS



TE Part #42863-2
RING CRIMP 12-10 AWG TPBR



TE Part #1586359-8
08P MINIMUMNL GANG WIRE SEAL DR




TE Part #2-216093-0
AMP-LATCH PRE-ASSY DIL WITHO



TE Part #215570-8
MICRO-MATCH PBC.08P



TE Part #964282-2
JPT A REC 2.8 Contact SWS Sn



TE Part #7-1123722-6
3.96 EP PLUG HSG 6P(NATURAL)



TE Part #9-1241961-9
STANDARD TIMER HOUSING MK II



TE Part #926984-2
STD TIMER CONTACT



TE Part #0068670009
TRSA-1019/G/1/PLUS

Documents

Product Drawings

187 FASTON,REC.,20-16 AWG,BR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_170037-4_AD.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_170037-4_AD.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_170037-4_AD.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

Japanese

Agency Approvals

[UL Report](#)

English