

**HDP26-24-19SE-L024**

✓ ACTIVE

DEUTSCH | DEUTSCH HDP, DEUTSCH HD

TE Internal #: YHDP26-24-19SEL024

19 Position Housing, Housing for Female Terminals, Wire-to-Wire,  
Sealable, Black, Wire & Cable, Power, Cable Mount (Free-Hanging),  
Hybrid

[View on TE.com >](#)[Connectors > Automotive Connectors > Automotive Housings > DEUTSCH HDP20 Housings](#)Number of Positions: **19**Connector & Housing Type: **Housing for Female Terminals**Mating Pin Diameter: **2.39 mm, 1.59 mm [.063 in, .094 in]**Connector System: **Wire-to-Wire**Sealable: **Yes**[All DEUTSCH HDP20 Housings \(357\)](#)

## Features

### Housing Features

Housing Material	PA GF
------------------	-------

### Industry Standards

IP Rating	IP67
UL Flammability Rating	20mm Flame Test per Standard UL-94

### Dimensions

Compatible Insulation Diameter Range	1.35 – 3.05 mm, 2.46 – 4.01 mm [.097 – .158 in] [.053 – .12 in]
Product Width	49.53 mm [1.95 in]
Product Length	38.3 mm [1.508 in]
Connector Height	49.53 mm [1.95 in]

### Packaging Features

Packaging Quantity	1
--------------------	---

## Packaging Method

Box

**Mechanical Attachment**

Strain Relief	Add By Accessory
Terminal Position Assurance	No
Mating Alignment Type	Guide Slot
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

**Other**

Serviceable	Yes
Connector Position Assurance Capable	No
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

**Electrical Characteristics**

Operating Voltage	250 VDC
Nominal Voltage Architecture	250 V

**Body Features**

Cable Exit Angle	180°
Primary Product Color	Black

**Contact Features**

Contact Size	Size 16, Size 12
Contact Type	Socket
Mating Pin Diameter	2.39 mm, 1.59 mm [.063 in][.094 in]
Contact Current Rating (Max)	25 A, 13 A

**Product Type Features**

Mixed & Hybrid Connector	Yes
Connector Shape	Circular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	Yes
Primary Locking Feature	Integrated in Housing
Connector & Contact Terminates To	Wire & Cable

**Configuration Features**

Blank Cavity Position	0
Connector Modification	Wide Threaded Adapter
Connector Seal Code	E Seal
Number of Positions	19

### Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

### Operation/Application

Circuit Application	Power
---------------------	-------

### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.5% in Component Part) Dodecamethylcyclohexasiloxane (D6) (.5% in Component Part) Decamethylcyclopentasiloxane (D5) (.5% in Component Part) <small>Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on

requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # HD30-24BT  
BOOT, 24SZ, ST, GRY



TE Part # HD30-24BT-90-BK  
BOOT, 24SZ, RA, BLK



TE Part # CAT-D48-ST273  
DEUTSCH Solid Contacts



TE Part # 1062-12-0166  
SOC, SF, SIZE 12, 12-14, NI/SN



TE Part # 0411-337-1205  
EXT TOOL, SIZE 12, 12-14 AWG, E,  
ORG



TE Part # 0411-336-1605  
EXT TOOL, SIZE 16, 16-20 AWG, E,  
DRK BLU



TE Part # CAT-D48-SP729  
DEUTSCH Sealing Plugs



TE Part # Y2428-024-24050000  
BKSHL, 24SZ, BLK, ST, L024, HDP



TE Part # CAT-H396-CH8172  
DEUTSCH HDP20 Housings



TE Part # 1062-12-0144  
SOC, SF, SIZE 12, 12-14, AU/SN



TE Part # 1062-12-0222  
SOC, SF, SIZE 12, 12-14, NI/NI



TE Part # CAT-J67-DSCC16  
DEUTSCH Size 16 Crimp Contacts




TE Part # HD30-24BT-BK  
BOOT, 24SZ, ST, BLK


Also in the Series | **DEUTSCH HD**




Automotive Connector Caps &amp; Covers (4)



Automotive Housings(357)




Connector Strain Relief(5)




Other Automotive Connector Accessories(6)


## Also in the Series | DEUTSCH HDP




Automotive Connector Caps &amp; Covers (4)




Automotive Housings(357)




Connector Backshells(10)



Connector Seals &amp; Cavity Plugs(1)



Insertion &amp; Extraction Tools(11)



Other Automotive Connector Accessories(6)

## Customers Also Bought

TE Part #HD16-9-16S  
PLG, 9P, GRY, N, 16TE Part #CAT-H396-CH8172  
DEUTSCH HDP20 HousingsTE Part #776524-4  
AS16,PLUG ASSY,ST,04P,E SEAL,  
CODE DTE Part #2325098-4  
MNTG CLIP,ENETSEAL PLUSTE Part #DTCE04-1-4P-LE03  
DTCE RECP ASM

## Documents

### Product Drawings

[PLG, 19P, BLK, E, WTHD, 12/16, S](#)

English

---

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_YHDP26-24-19SEL024\\_B.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_YHDP26-24-19SEL024\\_B.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_YHDP26-24-19SEL024\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[ICT Terminals and Connectors Catalogue](#)

English

[CONNECTOR SELECTOR](#)

English

---

### Product Specifications

[Application Specification](#)

English

---

### Agency Approvals

[UL Report](#)

English