



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **1**
Terminal Orientation: **Straight**
Primary Product Color: **Natural**

Features

Dimensions

Product Length	22.5 mm[.885 in]
----------------	------------------

Mechanical Attachment

Mating Alignment Type	None
Mating Alignment	Without

Product Type Features

Connector & Contact Terminates To	Wire & Cable
Sealable	No
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

--	--



Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	Without

Housing Features

Housing Material	Polyethylene
------------------	--------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Method	Carton
------------------	--------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>




EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 1-180984-2 FASTON 250 BOOT NYLON BLK	 TE Part # 180460 INSULATING BOOT POLYAMIDE NATURAL	 TE Part # 2-180930-1 250 FASTON HSG.,REC.,1 POS,RED	 TE Part # 8-180984-1 250 FASTON BOOT FLAG REC. 1P BLACK
 TE Part # 7-180984-0 250 FASTON BOOT FLAG REC. 1P NATURAL	 TE Part # 2-180984-0 FASTON BOOT 250 FLAG NYLON NAT	 TE Part # 280232-8 250 FASTON POST INS.,REC.,1 POS,NATURAL	 TE Part # 1-925017-0 250 FASTON HSG.,REC.,1 POS,NATURAL
 TE Part # 180984 FASTON 250 BOOT FLAG NYLON NAT	 TE Part # 2-180930-5 250 FASTON HSG.,REC.,1 POS,BLACK		

Also in the Series | FASTON 250

 Compression Connectors(4)	 Crimp Terminal Housings(132)	 Insertion & Extraction Tools(6)	 Magnet Wire Terminals(1)
--	--	--	---



PCB Terminals(134)



Quick Disconnects(425)



Splices(4)


Customers Also Bought



TE Part #1623763-2
23E 100KA 6.35X50FL B7 CAT



TE Part #150346-2
110 MINI FASTON,REC.,24-20 AWG, TPBR



TE Part #350536-1
UMNL SOK 20-14 .0126 PTPBR



TE Part #9-1437719-6
T01-0580-S03-FEMALE REC PANEL MNT SOLDER



TE Part #380635-1
RCR AU-SPR AU-CUP OE 018-040



TE Part #CAT-T3437-R819
RPS Commercial Grade Sleeves



TE Part #EC0054-000
05801914



TE Part #HUM-868-PRO-UFL
Module HUM-PRO 868MHz FHSS FM XCVR EU

Documents

Product Drawings

250 FASTON HSG.,REC.,1 POS,NATRUAL

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_2-180930-0_G1.3d_igs.zip

English

Customer View Model

ENG_CVM_2-180930-0_G1.3d_stp.zip

English

Customer View Model

ENG_CVM_2-180930-0_G1.2d_dxf.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_2-180930-0_G.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-180930-0_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-180930-0_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654742_HOUSEHOLD_APPLIANCES_RAST5](#)

English