

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
FB DIST
00

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	25JUN19	T.Q	W.H

NOTES:

1. MATERIAL: HOUSING - NYLON 66 (UL94V-0)
POST - TIN BRASSKINKING FORMING
4 PLACES

SECT E-E




4 Pos.




SECT E-E

KINKING FORMING
4 PLACES

5 Pos.

3 Pos.
SECT E-E2 Pos.
SECT E-ERECOMMENDABLE PCB LAYOUT
(PCB THK: 0.8-1.6)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MMTOLERANCES UNLESS
OTHERWISE SPECIFIED:
±0.2

Ø-PLC	±
1-PLC	±
2-PLC	±
3-PLC	±
4-PLC	±
ANGLES	±

MATERIAL

SEE NOTE

FINISH

, SEE NOTE

DWN 22JAN03

S.XU

CHK 22JAN03

S.YAO

APVD 22JAN03

T. SASAKI

PRODUCT SPEC

108-60016

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics Corporation
SHANGHAI, CHINAPOST HEADER ASS'Y POLARIZE TYPE (BOX-V TYPE)
(AMP CT CONNECTOR 2mm PITCH)

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-292131	

SCALE 5:1

SHEET 1 OF 2

REV A

RELEASED FOR PUBLICATION


© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1			



1.MATERIAL: HOUSING - NYLON 66 (UL94V-0)
POST - TIN BRASS



6~15 Pos.



RECOMMENDABLE PCB LAYOUT
(PCB THK:0.8-1.6)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

[illegible]

TOLERANCES UNLESS

OTHERWISE SPECIFIED:

	± 0.2
0. PLC	+

0 PLC	+
1 PLC	+

2 PLC	+ -
-------	-----

3	PLC	±
4	PLC	±

← PLZ ± -

ANGLES ± -

FINISH

DWIN

CHK

APVD

PRODUCT SPEC	
--------------	--

DATE: _____

—

~~WEIGHT~~

CUSTOMER DRAWING

tycò
Electronics

Tyco Electronics Corporation
SHANGHAI, CHINA

NAME

POST HEADER ASS'Y POLARIZE TYPE (BOX-V TYPE)
(AMP CT CONNECTOR 2mm PITCH)

SIZE	PRICE
Small	\$12.99
Medium	\$14.99
Large	\$16.99

CAGE CODE	
-----------	--

DRAWING NO

RESTRICTED TO

A3 00779 C-292131

SCALE 5:1

SHEET	2	OF	2
-------	---	----	---

REV	A
-----	---