

1-206070-1 ACTIVE

TE Internal #: 1-206070-1

Cable Clamp Kit, Thermoplastic, Black, Shell Size 17, 14.24 mm [.56 in] Cable Entry, UL 94V-0

[View on TE.com >](#)

Connectors > Connector Accessories > Connector Strain Relief

Strain Relief Accessory Type: **Cable Clamp Kit**Primary Product Material: **Thermoplastic**Primary Product Color: **Black**Compatible With Connector Shell Size: **17**Cable Entry Diameter: **14.24 mm [.56 in]**

Features

Housing Features

Compatible With Connector Shape	Circular
Body Orientation	Straight

Product Type Features

Strain Relief Accessory Type	Cable Clamp Kit
Sealable	No

Body Features

Primary Product Material	Thermoplastic
Primary Product Color	Black

Operation/Application

Compatible With Connector Shell Size	17
Shielded	No

Dimensions

Cable Entry Diameter	14.24 mm [.56 in]
----------------------	-------------------

Mechanical Attachment

Thread Size	5 – 20
-------------	--------

Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Bag
Packaging Quantity	1

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 206070-8
CABLE CLAMP KIT #17

Customers Also Bought



TE Part #206150-1
CPC PLUG ASSEMBLY SIZE 23-37



TE Part #206037-1
CPC PLUG ASSEMBLY SIZE 17-16



TE Part #1-206062-7
CABLE CLAMP KIT, BULK PKG



TE Part #206044-1
CPC PLUG ASSEMBLY SIZE 17-14




TE Part #182918-1
CPC SQ.FL.RCPT STD SEX



TE Part #66100-8
III+ SKT,18-16,15AU/FL,STRIP



TE Part #CAT-T4827-CH8172
Timer Connector Housing



TE Part #1-206138-0
CABLE CLAMP ASSY,BULK PACKED



TE Part #735222-1
FF 250 REC 1.0-2.5 MM2 0.32X19.30 BR

Documents

Product Drawings

CABLE CLAMP KIT #17

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1-206070-1_R.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-206070-1_R.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-206070-1_R.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.