

ROX9J110R

✓ ACTIVE

Neohm | Neohm ROX

TE Internal #: 2176416-9

Through-Hole General Purpose Resistor, Metal Oxide Film, 9 W,  
110 ohm, 5 %, ±350 ppm/°C, Axial-Leaded, Copper Termination, 54  
x 8.5 mm, Box, Neohm ROX

[View on TE.com >](#)



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **General Purpose Resistor**

Element Type: **Metal Oxide Film**

Power Rating: **9 W**

Resistance Class: **Up to 1kΩ**

Resistance Value: **110 Ω**

Features

Usage Conditions

|                             |              |
|-----------------------------|--------------|
| Operating Temperature Range | -55 – 155 °C |
| Temperature Coefficient     | ±350 ppm/°C  |

Electrical Characteristics

|                             |           |
|-----------------------------|-----------|
| Operating Voltage           | 750 V     |
| Power Rating                | 9 W       |
| Resistance Class            | Up to 1kΩ |
| Resistance Value            | 110 Ω     |
| Passive Component Tolerance | 5 %       |

Product Type Features

|               |                          |
|---------------|--------------------------|
| Resistor Type | General Purpose Resistor |
| Element Type  | Metal Oxide Film         |

Configuration Features

|                     |   |
|---------------------|---|
| Number of Resistors | 1 |
|---------------------|---|



Body Features

|           |              |
|-----------|--------------|
| Lead Type | Axial-Leaded |
|-----------|--------------|

Termination Features

|                                |        |
|--------------------------------|--------|
| Termination Area Base Material | Copper |
| Number of Terminations         | 2      |

Dimensions

|                              |             |
|------------------------------|-------------|
| Passive Component Dimensions | 54 x 8.5 mm |
|------------------------------|-------------|

Packaging Features

|                  |     |
|------------------|-----|
| Packaging Method | Box |
|------------------|-----|

Other

|                    |           |
|--------------------|-----------|
| EU RoHS Compliance | Compliant |
| EU ELV Compliance  | Compliant |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JUNE 2023 (235)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                             |
| Solder Process Capability                     | Wave solder capable to 265°C                                                                                                    |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 4-1625886-1  
1W SM M/OX 5% 820K



TE Part # 1625893-5  
5W SM M/OX 5% 47K



TE Part # 1625881-2  
1W STD M/OX 2% 220R



TE Part # 2-1625892-1  
3W SM M/OX 5% 1K0



TE Part # 6-1676123-7  
1/2W SM M/OX 5% 470R

Also in the Series | Neohm ROX



Through-Hole Resistors(783)

Customers Also Bought



TE Part #2-1625931-5  
MCU 100K 10% 1"PL



TE Part #8-1419111-0  
PT570012



TE Part #4-1415033-1  
PT78740



TE Part #3-1393115-3  
KUL-11D15D-48=KU







TE Part #1622526-1  
LR1 1% 5K1



TE Part #1-1478419-0  
N Str Plg PS 50Ohm Silver Pltd RG58C /U,




TE Part #166916-000  
RMW-63/19-1200/ADH-0



TE Part #2-1768020-4  
ESSW74-052



TE Part #ADP-SMAF-MCXM  
SMA Jack to MCX Plug



TE Part #1SNA163911R1400  
FX M5/M3 NOIR

Documents

Product Drawings

9W STD M/OX 5% 110R

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2176416-9\_BA.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2176416-9\_BA.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2176416-9\_BA.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Flame Proof Power Metal Oxide Film Resistors - Type ROX Series - Tyco Electronics Passives

English