

Kemtron | Kemtron 1201 Series

TE Internal #: 2420750-1

Extruded EMI Gasket, Conductive Strip, Fluorosilicone Binding, Silver Plated Aluminum (Ag/Al) Filler, Solid Round, Kemtron 1201 Series

[View on TE.com >](#)

EMI & EMC Solutions > EMI Shielding > EMI Gaskets > Extruded EMI Gasket Conductive Strip



Gasket Type: Extruded EMI Gasket

Finished Type: Conductive Strip

Binding Material: Fluorosilicone

Filler Material: Silver Plated Aluminum (Ag/Al)

Gasket Shape: Solid Round

[All Extruded EMI Gasket Conductive Strip \(56\)](#)

Features

Body Features

Gasket Type	Extruded EMI Gasket
Gasket Shape	Solid Round

Product Type Features

Finished Type	Conductive Strip
Binding Material	Fluorosilicone
Filler Material	Silver Plated Aluminum (Ag/Al)

Dimensions

Product Length	1 m[3.28 ft]
Outside Diameter	1.8 mm[.07 in]

Usage Conditions

Operating Temperature Range	-55 – 160 °C[-67 – 320 °F]
-----------------------------	----------------------------

Electrical Characteristics

Resistance to Petroleum	Yes
Volume Resistivity (Max)	.012 Ω.cm

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: DCP (.32% in Component) <small>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2452655-1
SNA Cord 1.8mm x 1m LTE Part # CAT-EMIG-0001
Extruded EMI Gasket Conductive Strip

Also in the Series | Kemtron 1201 Series










EMI Gaskets(48)



Medical EMI & EMC Solutions(48)

Customers Also Bought

TE Part #281698-4
HEADER HE14 RA 4 PTE Part #281695-4
HEADER HE14 STRAIGHT 4 PTE Part #282838-2
TERMI-BLOK PCB MOUNT 90 2P.TE Part #1776112-3
3P,2.60MM, SIDE ENTRY, HIGH TMPTE Part #284392-6
TERMI-BLOK PCB SIDE ENTRY STACTE Part #1-284392-2
TERMI-BLOK PCB SIDE ENTRY STACTE Part #L9000029-01
Antenna 1/4 Wave R-Angle 2.4GHz RPSTE Part #3-2176339-1
CRGCQ 0603 3K3 1%TE Part #6-2176455-0
CPF 0402 453K 0.1% 25ppm 1K RLTE Part #440360-2
.8MM FAX MODEM SOCKET 124P,
7.95H

Documents

Product Drawings

[FSA Cord 1.8mm x 1m L](#)

English

Datasheets & Catalog Pages

[Performance Materials brochure](#)

English

Datasheet - Conductive Elastomers

English

Product Specifications

[Application Specification](#)

English