

221265-1

X OBSOLETE

AMP | BNC

TE Internal #: 221265-1

TE Internal Description: PLUG,CATEGORY A,SERIES BNC

[View on TE.com >](#)

Connectors > RF Connectors > Coax Connectors



RF Interface: BNC

RF Connector Style: Plug

RF Connector Mated Outer Diameter (Approximate): 14.53 mm [.572 in]

Impedance: 50 Ω

Compatible With RF Cable Type: RG 223, RG 58C, RG 58B, RG 142B, RG 58A, RG 55, RG 141A, RG 55A, RG 141, RG 142, RG 58, RG 142A, RG 55B, RG 400

Features

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Other

Coupling Nut Base Material	Brass
Grade	Military
Dielectric Material	PTFE
EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Contact Features

RF Connector Center Contact Underplating Material	Nickel
RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Brass

Product Type Features

Connector Seal & Plug Type	Interfacial Seal
Connector Shape	Circular
RF Interface	BNC
RF Connector Style	Plug
Compatible With RF Cable Type	RG 223, RG 58C, RG 58B, RG 142B, RG 58A, RG 55, RG 141A, RG 55A, RG 141, RG 142, RG 58, RG 142A, RG 55B, RG 400

Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Dimensions

RF Connector Mated Outer Diameter (Approximate)	14.53 mm[.572 in]
---	-------------------

Electrical Characteristics

Impedance	50 Ω
-----------	------

Mechanical Attachment

RF Connector Coupling Mechanism	Bayonet
RF Contact Captivation Method	Mechanical

Operation/Application

Operating Frequency	4 GHz
---------------------	-------

Configuration Features

Number of Positions	1
Number of Coaxial Contacts	1

Body Features

Cable Connector Orientation	Straight
Body Material	Brass
Body Material Finish	Plated
Body Plating Material	Silver

Termination Features

Termination Method to Wire & Cable	Solder & Clamp
------------------------------------	----------------

Packaging Features

Packaging Method	Carton
------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240)

SVHC > Threshold:
Pb (4% in Contact/Component)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free


Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | BNC



Coax Connectors(8)

Customers Also Bought



TE Part #205203-3
CRIMP SNAP RCPT ASSY,SIZE 1



TE Part #205205-2
CRIMP SNAP RCPT ASSY,SIZE 2



TE Part #5-1879208-0
CPF 0402 1K1 0.1% 25PPM 1K RL



TE Part #2311768-2
AMPL REC, HD22, R/A, 26P, S/L



Documents

CAD Files

Customer View Model

[ENG_CVM_221265-1_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_221265-1_H.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_221265-1_H.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English

[Connector, BNC, Field Serviceable, Category A](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[50-OHM RF SERIES BNC PLUG CONNECTORS 221265-\[\] \(FIELD SERVICEABLE\)](#)

English