



Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Number of Positions: 12

Terminal Block Connector Type: **Header**

Connector System: **Wire-to-Board**

Centerline (Pitch): **5 mm [.197 in]**

Number of Rows: 1

Features

Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	3.5 mm[.138 in]

Identification Marking

Marking Color	White
---------------	-------

Body Features

Primary Product Color	Green
Product Orientation	Right Angle

Packaging Features

Packaging Method	Box
Packaging Quantity	100

Contact Features

Contact Mating Area Plating Material	Tin
Contact Base Material	Copper Alloy



Contact Current Rating (Max)	15 A
------------------------------	------

Housing Features

Housing Material	PA 66
Centerline (Pitch)	5 mm[.197 in]

Product Type Features

Header Type	Fully Shrouded
Terminal Block Connector Type	Header
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Stacking Configuration	Side Stackable
Number of Positions	12
Number of Rows	1

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Dimensions

Wire Size	30 – 12 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant




China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 1-1546557-2
12P, SCREWLESS CLIP PLUG, 5.0MM



TE Part # 1-796640-2
12 POS 5.0 MM R/A PLUG, TRM BLK




TE Part # 1-284040-2
TERMI-BLOK VERTICAL PLUG STACK



TE Part # 1-1776148-2
12P TERMI-BLOK HDR, HIGH TEMP



TE Part # 1-796641-2
12 POS 5.0 MM R/A PLUG, TRM BLK



TE Part # 1-284046-2
TERMI-BLOK VERTICAL PLUG STACK

Customers Also Bought




TE Part #2-1419106-1
27E489=SOCKET,K10,8,PCB,NYL



TE Part #66103-1
III+ PIN,24-20,30AU>10,LP



TE Part #1825002-5
ADF0404=DIP SWT,FLUSH,THRU/HL



TE Part #1825069-1
C23004 CAP BLACK




TE Part #1977740-2
MPS103FPC PSHBTN SPDT MMNTRY



TE Part #8-1437627-7
G13A=BUTTON GUARD ALUM



TE Part #2176093-5
RP 2A 0.25W 10K 0.1% 25PPM 1K RL



TE Part #1-2350513-2
12POS TB HDR 90 DEG, PITCH 5.0 &TL 4.5mm



TE Part #1623257-1
CRG0805 1% 5K1



TE Part #2267473-1
SIZE 11 PERIPHERAL SEAL, CPC

Documents

Product Drawings

12POS 5.0MM CE R/A HDR,TRM BLK

English

CAD Files

Customer View Model

ENG_CVM_1-796644-2_C1.3d_igs.zip

English

Customer View Model

ENG_CVM_1-796644-2_C1.2d_dxf.zip

English

3D PDF

English

Customer View Model

ENG_CVM_1-796644-2_C1.3d_stp.zip

English

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_1-796644-2_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-796644-2_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-796644-2_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Eurostyle Terminal Blocks Focus Product Stock List](#)

English

[BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS](#)

English

[BUCHANAN PCB TERMINAL BLOCKS](#)

English

[1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL](#)

English