



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Precision Resistor**
Element Type: **Thin Film**
Power Rating: **1 W**
Resistance Class: **1kΩ – 1MΩ**
Resistance Value: **3.3K Ω**

Features

Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±100 ppm/°C

Electrical Characteristics

Operating Voltage	500 V
Power Rating	1 W
Resistance Class	1kΩ – 1MΩ
Resistance Value	3.3K Ω
Passive Component Tolerance	1 %

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film

Configuration Features

Number of Resistors	1
---------------------	---

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2



Dimensions

Passive Component Dimensions	10 x 3.7 mm
------------------------------	-------------

Packaging Features

Packaging Method	Bandoliered
------------------	-------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

H4P3K3FZA


Through-Hole Precision Resistor, Thin Film, 1 W, 3.3K ohm, 1 %, ±100 ppm/°C, Axial-Leaded, Copper Termination, 10 x 3.7 mm, Holsworthy Holco




TE Part # 5-1879642-1
[H8 5K0 0.1% 25PPM](#)



TE Part # 1879623-8
[H4 1K3 0.1% 5PPM](#)



TE Part # 2-1879622-2
[H4P 1M0 1% 50PPM](#)



TE Part # 9-1879664-1
[H8 10K 0.1% 15PPM](#)



TE Part # 1879629-8
[H4P 127R 0.5% 5PPM](#)

Also in the Series | [Holsworthy Holco](#)



[Through-Hole Resistors\(6370\)](#)

Customers Also Bought




TE Part #1462042-9
[IMC06CGR=IM Relay 140mW 12V 1CO](#)



TE Part #2-1879461-2
[RL73H 2A R10 1% 1K RL](#)



TE Part #4-1879214-5
[CPF 0402 953R 0.1% 25PPM 1K RL](#)




TE Part #9-1879663-4
[H8 1K0 0.1% 15PPM](#)




TE Part #8-2176091-7
[RP 2A 0.25W 475R 0.1% 25PPM 1K RL](#)




TE Part #213768-4
[PIN HDR ASSY,23P,MMATE LF](#)



TE Part #1879664-3
[H8 1K21 0.1% 15PPM](#)



TE Part #4-1879267-7
[RP 2B 976K 0.1% 15PPM 1K RL](#)



Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_6-1879627-1_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-1879627-1_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-1879627-1_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English

Axial Leaded Precision Resistors - Type HOLCO Series

English

[8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS](#)

English